
JK-SMD1210-075-24 PPTC DEVICES Part Number: Q/JKTD-24-075

Pb RoHS



Edition: AO

Page No: 1 OF 3



Terminal pad materials :Tin-Plated Nickle-copper

Terminal pad solderability : Meets EIA specification RS 186-9E and ANSI/J-STD-002 Category 3.

Marking : JA=1210(075)

Table1 :DIMENTION(Unit : mm)

Madal	Marking	А		В		С		D
Model		Min.	Max.	Min.	Max.	Min.	Max	Min.
JK-SMD1210-075	JA	3.00	3.43	2.35	2.80	0.6	1.3	0.25

Table2 :PERFORMANCE RATINGS:

Model	V_{max}	I _{max}	Ihold	I _{trip}	Itrip Pd 25°C Typ (A) (W)	Maximum Time To Trip		Resistance		
Model	(Vdc)	(A)	@25°C (A)			Current	Time	Ri _{min}	Ri _{typ}	$R1_{max}$
						(A)	(Sec)	(Ω)	(Ω)	(Ω)
JK-SMD1210-075	24	100	0.75	1.50	0.6	8.0	0.10	0.070	0.230	0.45

Table3:Test Conditons and Standards

Item	Test Conditon	Standard			
Initial Resistance	25°C	$0.070{\sim}0.450\Omega$			
I _H	25°C, 0.75A, 60min	No Trip			
Ttrip	25°C, 8.0A	≤0.10s			
Trip endurance	24V, 100A, 60min	No arcing or burning			

Operating Temperature: -40℃ TO 85℃ Packaging: Bulk ,4000pcs per bag


SHENZHEN JINRUI ELECTRONIC MATERIAL CO.,LTD6 F DISTRICT NO. 300INDUSTRY PARKSHANGKENG COMMUNITY GUANLAN STREET BAOAN SHENZHEN

6 F DISTRICT NO. 3000046 BLDG Hi-Tech SCIENCE &

JK-SMD1210-075-24 PPTC DEVICES Part Number: Q/JKTD-24-075



Solder reflow conditions



Profile Feature	Pb-Free Assembly 3°C/second max.			
Average ramp up rate (Ts _{MAX} to Tp)				
Preheat				
 Temperature min. (Ts_{MIN}) 	150°C			
 Temperature max. (Ts_{MAX}) 	200°C			
 Time (ts_{MIN} to ts_{MAX}) 	60-120 seconds			
Time maintained above:				
• Temperature (T _L)	217°C			
• Time (t _L)	60-150 seconds			
Peak/Classification temperature (Tp)	260°C			
Time within 5°C of actual peak temperat	ure			
Time (tp)	30 seconds max.			
Ramp down rate	3°C/second max.			
Time 25°C to peak temperature	8 minutes max.			

- Recommended reflow methods: IR, vapor phase oven, hot air oven, N2 environment for lead-free.
- Devices are not designed to be wave soldered to the bottom side of the board.
- Recommended maximum paste thickness is 0.25mm (0.010inch).
- Devices can be cleaned using standard industry methods and solvents.
- Soldering temprature profile meets RoHs leadfree process.

Note: All temperatures refer to topside of the package, measured on the package body surface.

Notes: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements

SHENZHEN JINRUI ELECTRONIC MATERIAL CO.,LTD6 F DISTRICT NO. 3000046 BLDG Hi-Tech SCIENCE &INDUSTRY PARKSHANGKENG COMMUNITY GUANLAN STREET BAOAN SHENZHEN

Edition: AO

Page No: 2 OF 3



JK-SMD1210-075-24 PPTC DEVICES Part Number: Q/JKTD-24-075


Edition: AO

Page No: 3 OF 3





Recommended pad layout (mm)



WARNING

 \cdot Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.

• PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.

 \cdot Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.

· Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.

· Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.

 \cdot Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices.PPTC SMD can be cleaned by standard methods.

 \cdot Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profilecould negatively impact solderability performance of our devices.

SHENZHEN JINRUI ELECTRONIC MATERIAL CO.,LTD6 F DISTRICT NO. 3000046 BLDG Hi-Tech SCIENCE &INDUSTRY PARKSHANGKENG COMMUNITY GUANLAN STREET BAOAN SHENZHEN