





SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass (H65) Tin-plated



PCB LAYOUT

编号	尺寸 (mm)		
	A	B	C
PHB-2*2A	2.00	6.00	3.00
PHB-2*3A	4.00	8.00	3.00
PHB-2*4A	6.00	10.00	3.00
PHB-2*5A	8.00	12.00	5.00
PHB-2*6A	10.00	14.00	7.00
PHB-2*7A	12.00	16.00	9.00
PHB-2*8A	14.00	18.00	11.00
PHB-2*9A	16.00	20.00	13.00
PHB-2*10A	18.00	22.00	15.00
PHB-2*11A	20.00	24.00	17.00
PHB-2*12A	22.00	26.00	19.00
PHB-2*13A	24.00	28.00	21.00
PHB-2*14A	26.00	30.00	23.00
PHB-2*15A	28.00	32.00	25.00
PHB-2*16A	30.00	34.00	27.00
PHB-2*17A	32.00	36.00	29.00
PHB-2*18A	34.00	38.00	31.00
PHB-2*19A	36.00	40.00	33.00
PHB-2*20A	38.00	42.00	35.00

联系电话 18058866958

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生	料号 PART NO.	PHB-2*NA	版本 REV.	A		
			X.±0.25	X.*±2°		2013、07、01		品名 TITLE		PHB直针	页次 SHEET	1/1
			.X±0.20	.X*±1°		张名		客户料号 CUTM. NO.		WAFER DIP TYPE		
			XX+0 15	XX*+0 5°		2013、07、03		张名				
					核准	张名	1:1 深圳市华灿天禄电子有限公司					