


SPECIFICATION FOR APPROVAL

CUSTOMER		CUST P/N.	
ITEM	Data Line Filter	Description	BCB0308WN-301
PART NO.	302-69050	DATE	2017.07.13

(1) DIMENSION(UNIT:mm)



A	10.5MAX	mm
B	7.0 ± 0.5	mm
C	3.5 ± 0.5	mm
D	7.5 (Max)	mm
E	7.5 ± 0.5	mm
F	5.0 ± 0.5	mm
G	Ø0.6(REF)	mm
H		mm

(2) ELECTRICAL REQUIREMENTS

	TEST CONDITION	FREQUENCY	VOLTAGE	(3) TEST INSTRUMENTS	
				LCR-METER:	
Z₁	305 Ω (Min)	25MHz	0.25V	V	HP4291A
Z₂	460 Ω (Min)	100MHz	0.25V	V	HP4291A
DCR	15.0mΩ±20%	KHz	V	V	WK3260B
L₁=L₂	12.0uH(REF)	100K	1V	V	WK3260B
				V	TH2816B
IDC	3.5 A(Max)	MHz	V	GW PUNCTURE INSULATION TESTER	
				V	TH2816+1320

(4) TURNS: 7Ts(REF)

(5) MATERIAL LIST

ITEM	MATERIAL	DESCRIPTION	UL NO.
1	CORE	T 7×5×3-C	
2	WIRE	Ø0.4mm×2(2UEW+NY)	E197768
3	BASE	B025	E59481

REMARK:	APPROVED	CHECKED	DRAWN BY
	姜杰文	姜法寶	王艷