



CUT-OUT

Nut Torque: 5 ~ 14Nm
 Operating Pressure: 400gf ±100gf
 Operating Stroke: 0.6mm±0.3
 Protection Grade: IP67
 Function: (ON)-OFF
 Shell: SUS
 Button: SUS
 Rating: 50mA 12V DC
 Contact Resistance: 50mΩ MAX.
 Insulation Resistance: 100MΩ MIN.
 Dielectric Strength: 1500V AC 1 minute
 Electrical life: 50,000 cycles
 Mechanical life: 200,000 cycles
 Operating Temperature: -20°C~80°C
 Relative Air Humidity: 45%~85%
 Safety Approval:



D-SWITCH
 东莞市德松电子有限公司
 D-SWITCH ELECTRONICS CO.,LTD

公差 TOLERANCES .X±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.
版本	核准	比例尺 SCALE	1:1	日期 DATE	2021.01.25	品名 TITLE	图号 DRAWING NO
公差 TOLERANCES	角度 ANGLE	单位 DIMENSION UNIT	mm.	品名 TITLE	PBM-12Q11-RT-N-NN-S7S	图号 DRAWING NO	PBM-12Q11-RT-N-NN-S7S_A0
版本	核准	比例尺 SCALE	1:1	日期 DATE	2021.01.25	品名 TITLE	图号 DRAWING NO
公差 TOLERANCES	角度 ANGLE	单位 DIMENSION UNIT	mm.	品名 TITLE	PBM-12Q11-RT-N-NN-S7S	图号 DRAWING NO	PBM-12Q11-RT-N-NN-S7S_A0
版本	核准	比例尺 SCALE	1:1	日期 DATE	2021.01.25	品名 TITLE	图号 DRAWING NO
公差 TOLERANCES	角度 ANGLE	单位 DIMENSION UNIT	mm.	品名 TITLE	PBM-12Q11-RT-N-NN-S7S	图号 DRAWING NO	PBM-12Q11-RT-N-NN-S7S_A0