


MMBT3906W

PNP Silicon Epitaxial Planar Transistor

for switching and amplifier applications

Marking Code: 3N



1.Base 2.Emitter 3.Collector
SOT-323 Plastic Package

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Collector Base Voltage	$-V_{CBO}$	40	V
Collector Emitter Voltage	$-V_{CEO}$	40	V
Emitter Base Voltage	$-V_{EBO}$	5	V
Collector Current	I_C	200	mA
Total Power Dissipation	P_{tot}	200	mW
Junction Temperature	T_j	150	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	- 55 to +150	$^\circ\text{C}$

MMBT3906W

Characteristics at $T_a = 25^\circ\text{C}$

Parameter	Symbol	Min.	Max.	Unit
DC Current Gain at $-V_{CE} = 1 \text{ V}$, $-I_C = 0.1 \text{ mA}$	h_{FE}	60	-	-
at $-V_{CE} = 1 \text{ V}$, $-I_C = 1 \text{ mA}$	h_{FE}	80	-	-
at $-V_{CE} = 1 \text{ V}$, $-I_C = 10 \text{ mA}$	h_{FE}	100	300	-
at $-V_{CE} = 1 \text{ V}$, $-I_C = 50 \text{ mA}$	h_{FE}	60	-	-
at $-V_{CE} = 1 \text{ V}$, $-I_C = 100 \text{ mA}$	h_{FE}	30	-	-
Collector Emitter Cutoff Current at $-V_{CE} = 30 \text{ V}$	$-I_{CES}$	-	50	nA
Emitter Base Cutoff Current at $-V_{EB} = 3 \text{ V}$	$-I_{EBO}$	-	50	nA
Collector Base Breakdown Voltage at $-I_C = 10 \mu\text{A}$	$-V_{(BR)CBO}$	40	-	V
Collector Emitter Breakdown Voltage at $-I_C = 1 \text{ mA}$	$-V_{(BR)CEO}$	40	-	V
Emitter Base Breakdown Voltage at $-I_E = 10 \mu\text{A}$	$-V_{(BR)EBO}$	5	-	V
Collector Emitter Saturation Voltage at $-I_C = 10 \text{ mA}$, $-I_B = 1 \text{ mA}$ at $-I_C = 50 \text{ mA}$, $-I_B = 5 \text{ mA}$	$-V_{CE(sat)}$	- -	0.25 0.4	V
Base Emitter Saturation Voltage at $-I_C = 10 \text{ mA}$, $-I_B = 1 \text{ mA}$ at $-I_C = 50 \text{ mA}$, $-I_B = 5 \text{ mA}$	$-V_{BE(sat)}$	0.65 -	0.85 0.95	V
Transition Frequency at $-V_{CE} = 20 \text{ V}$, $I_E = 10 \text{ mA}$, $f = 100 \text{ MHz}$	f_T	250	-	MHz
Collector Output Capacitance at $-V_{CB} = 10 \text{ V}$, $f = 100 \text{ KHz}$	C_{ob}	-	4.5	pF
Delay Time at $-V_{CC} = 3 \text{ V}$, $-V_{BE(OFF)} = 0.5 \text{ V}$, $-I_C = 10 \text{ mA}$, $-I_{B1} = 1 \text{ mA}$	t_d	-	35	ns
Rise Time at $-V_{CC} = 3 \text{ V}$, $-V_{BE(OFF)} = 0.5 \text{ V}$, $-I_C = 10 \text{ mA}$, $-I_{B1} = 1 \text{ mA}$	t_r	-	35	ns
Storage Time at $-V_{CC} = 3 \text{ V}$, $-I_C = 10 \text{ mA}$, $I_{B1} = -I_{B2} = -1 \text{ mA}$	t_{stg}	-	225	ns
Fall Time at $-V_{CC} = 3 \text{ V}$, $-I_C = 10 \text{ mA}$, $I_{B1} = -I_{B2} = -1 \text{ mA}$	t_f	-	75	ns

MMBT3906W




Fig.1 Grounded emitter output characteristics




Fig.2 Collector-emitter saturation voltage vs. collector current




Fig.3 DC current gain vs. collector current (I)




Fig.4 DC current gain vs. collector current (II)

MMBT3906W




Fig.8 Turn-on time vs. collector current




Fig.9 Rise time vs. collector current




Fig.10 Storage time vs. collector current




Fig.11 Fall time vs. collector current




Fig.6 Base-emitter saturation voltage vs. collector current




Fig.10 Power Dissipation vs Ambient Temperature