

## Features

- ◆ Ultra low capacitance: 0.1 pF typical (I/O to I/O)
- ◆ Ultra low leakage: nA level
- ◆ Low operating voltage: 3.3V
- ◆ Low clamping voltage
- ◆ Up to 4 data lines and one power line protects
- ◆ Complies with following standards:
  - IEC 61000-4-2 (ESD) immunity test
    - Air discharge: ±20kV
    - Contact discharge: ±15kV
  - IEC61000-4-4 (EFT) 40A (5/50ns)
  - IEC61000-4-5 (Lightning) : 6 A(8/20μs)
- ◆ ROHS Compliant

## Mechanical Characteristics

- ◆ Package: DFN2510-10 (2.5×1.0×0.5mm)
- ◆ Ultra low leakage: nA level
- ◆ Case Material: "Green" Molding Compound.
- ◆ UL Flammability Classification Rating 94V-0
- ◆ Moisture Sensitivity: Level 3 per J-STD-020
- ◆ Terminal Connections: See Diagram Below



## Applications

- ◆ High Definition Multimedia Interface (HDMI)
- ◆ Digital Visual Interface (DVI)
- ◆ Unified Display Interface (UDI)
- ◆ MDDI Ports
- ◆ PCI Express
- ◆ Serial ATA


## Ordering Information

| Part Number    | Qty per Reel | Reel Size |
|----------------|--------------|-----------|
| TPESD7504MUTAG | 3000         | 7"        |

## Dimensions and Pin Configuration



MARKING CODE:



30 = Specific Device Code  
xxyy = Date Code

**Absolute Maximum Ratings** (Tamb=25°C unless otherwise specified)

| Parameter                       | Symbol | Value       | Unit |
|---------------------------------|--------|-------------|------|
| Peak Pulse Current (8/20μs)     | Ipp    | 6           | A    |
| ESD per IEC 61000-4-2 (Air)     | VESD   | ±20         | kV   |
| ESD per IEC 61000-4-2 (Contact) |        | ±15         |      |
| Operating Temperature Range     | TJ     | -55 to +125 | °C   |
| Storage Temperature Range       | Tstg   | -55 to +150 | °C   |

**Electrical Characteristics** (TA=25°C unless otherwise specified)

| Parameter               | Symbol | Min | Typ  | Max  | Unit | Test Condition                        |
|-------------------------|--------|-----|------|------|------|---------------------------------------|
| Reverse Working Voltage | VRWM   |     |      | 3.3  | V    |                                       |
| Trigger Voltage         | Vt1    | 6   |      | 9    | V    | IT = 1mA                              |
| Holding Voltage         | Vh     | 2   |      | 3    | V    | Ih = 1mA                              |
| Reverse Leakage Current | IR     |     |      | 0.08 | uA   | VRWM = 3.3V                           |
| Clamping Voltage        | VC     |     | 5    |      | V    | Ipp=6A(8x 20us pulse)                 |
| Clamping Voltage        | VC     |     | 5.2  |      | V    | Ipp=8A(100ns pulse)                   |
| Clamping Voltage        | VC     |     | 7.5  |      | V    | Ipp=16A(100ns pulse)                  |
| Junction Capacitance    | CJ     |     | 0.18 | 0.3  | pF   | VR = 0V, f = 1MHz, Between IO and GND |
| Junction Capacitance    | CJ     |     | 0.1  | 0.2  | pF   | VR = 0V, f = 1MHz, Between IO and IO  |

**Typical Performance Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise Specified)**

Fig1. 8/20 $\mu\text{s}$  Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve



**Outline Drawing - DFN2510-10**



**Land Pattern - DFN2510-10**

