

雅晶鑫電子

TAXD26M2BLDBET2S

● ELECTRICAL PARAMETERS

谐振器产品技术指标		Min	Max	Units
1.Holder Type(型号规格)		AT 206		
3. Frequency (标称频率)		26.000000		MHz
4.Load Capacitance (CL) (负载电容)		20		pF
5.Drive Level (激励功率)		10.000		uw
6.Equivalent Resistance (谐振电阻)			25	Ω
7.Shunt Capacitance (Co) (静态电容)		0	7	pF
9.Frequency Tolerance at 25℃ (调整频差)		-20	20	ppm
11.Insulation Resistance (at DC 100V) (绝缘电阻)		500		MΩ
12.Operating Temperature Range (工作温度范围)		-20	70	℃
13. Storage Temperature Range (储存温度范围)		-20	70	℃
14. Aging (老化率)		± 5		ppm/year
15. DLD2	N/A		N/A	Ω
16. FLD2			N/A	ppm
17. RLD2			N/A	Ω
18. SPDB			N/A	db
19. Other (其它)		N/A		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)

FREQUENCY VS. TEMPERATURE CURVE

