


● ELECTRICAL PARAMETERS

谐振器产品技术指标		Min	Max	Units
1.Holder Type(型号规格)		SEAM 206		
3. Frequency (标称频率)		75. 000000		KHz
4.Load Capacitance (CL) (负载电容)		12. 5		pF
5.Drive Level (激励功率)		1. 000		uw
6.Equivalent Resistance (谐振电阻)			35	KΩ
7.Shunt Capacitance (Co) (静态电容)		0	1. 5	pF
8.Motional Capacitance (C1) (动态电容)		0. 0028		fF
9.Frequency Tolerance at 25°C (调整频差)		-50	50	ppm
10.Temperature Coefficient 二次温度系数		[-0. 035±0. 01]ppm/°C		
11.Insulation Resistance (at DC 100V) (绝缘电阻)		500		MΩ
12.Operating Temperature Range (工作温度范围)		-20	70	°C
13. Storage Temperature Range (储存温度范围)		-40	85	°C
14. Aging (老化率)		± 5		ppm/year
15. DLD2	N/A		N/A	Ω
16. FLD2			N/A	ppm
17. RLD2			N/A	Ω
18. SPDB			N/A	db
19. Other(其它)		N/A		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)



FREQUENCY VS. TEMPERATURE CURVE

