





## 6A SURFACE MOUNT BRIDGE RECTIFIER

### FEATURES:

- Reverse Voltage - 800 & 1000 V
- Forward Current - 6.0 A
- High Surge Current Capability
- Designed for Surface Mount Application

### PINNING

PIN	DESCRIPTION
1	Output Anode ( + )
2	Output Cathode ( - )
3	Input Pin ( ~ )
4	Input Pin ( ~ )



ULBF Package

### MECHANICAL DATA

- Case: ULBF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.461g / 0.0163oz

### Maximum Ratings and Electrical characteristics







Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	ULBF608	ULBF610	Units	
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	800	1000	V	
Maximum RMS voltage	$V_{RMS}$	560	700	V	
Maximum DC Blocking Voltage	$V_{DC}$	800	1000	V	
Average Rectified Output Current	$I_o$	6.0			A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	$I_{FSM}$	200			A
$I^2t$ Rating for Fusing	$I^2t$	166			$A^2S$
Maximum Forward Voltage at 1.0 A	$V_F$	0.83 (typ.)			V
Maximum Forward Voltage at 6.0 A	$V_F$	1.0			V
Maximum DC Reverse Current @ $T_A=25^\circ C$ @ $T_A=125^\circ C$	$I_R$	5 100			$\mu A$
Typical Junction Capacitance ( Note1 )	$C_j$	100			pF
Typical Thermal Resistance ( Note2 )	$R_{\theta JA}$ $R_{\theta JC}$ $R_{\theta JL}$	60 10 12			°C/W
Operating and Storage Temperature Range	$T_j, T_{stg}$	-55 ~ +150			°C

Note: 1. Measured at 1MHz and applied reverse voltage of 4 V D.C.

2. Mounted on glass epoxy PC board with 4×1.5"×1.5" ( 3.81×3.81 cm ) copper pad.







## PACKAGE OUTLINE

Plastic surface mounted package; 4 leads

ULBF



### The recommended mounting pad size



### Marking

Type number	Marking code
ULBF608	ULBF608
ULBF610	ULBF610