LOW POWER LOW OFFSET VOLTAGE SINGLE COMPARATOR

Features

I Wide Supply Voltage RangeI Single Supply: 2.0V to 36V

I Dual Supplies: ±1.0V to ±18V

I Low Supply Current at VCC=5V: 0.4mA

I Low Input Bias Current: 25nA (Typ)I Low Input Offset Current: 5nA (Typ)

I Low Input Offset Voltage: ±1mV (Typ)

I Input Common Mode Voltage Range Includes

Ground

- Differential Input Voltage Range Equals to the Power Supply Voltage
 - Low Output Saturation Voltage: 200mV at 4mA
- I Open Collector Output
- I Small Package:

GS331 Available in SOT23-5 Package

General Description

The GS331 consists of a single precision voltage com-parator with a typical input offset voltage of 1.0mV and high voltage gain. It is specifically designed to operate from a single power supply over wide range of voltages. Operation from split power supply is also possible and the low power supply current drain is independent of the magnitude of the power supply voltage.

The GS331 is available in standard SOT-23-5 package.

Applications

- I Battery Charger
- Cordless Telephone
- I Switching Power Supply

- I DC-DC Module
- I PC Motherboard
- I Communication Equipment

Pin Configuration




Figure 1. Pin Assignment Diagram





March 2020-REV_V0 1/10



Functional Block Diagram




Figure 2. Functional Block Diagram of GS331

Absolute Maximum Ratings

Condition	Symbol	Max
Power Supply Voltage	Vcc	±20V or 40V
Differential input voltage	V _{I(DIFF)}	40V
Input Voltage	Vı	-0.3V~40V
Operating Junction Temperature	TJ	150°C
Storage Temperature Range	Tstg	-65°C ~+150°C

Note 1: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Max-imum Ratings" for extended periods may affect device reliability.

Note 2: This input current will only exist when the voltage at any of the input leads is driven negative. It is due to the collector-base junction of the input PNP transistors becoming forward biased and thereby acting as input diode clamps. In addition to this diode action, there is also lateral NPN parasitic transistor action on the IC chip. This transistor action can cause the output voltages of the comparators to go to the V+ voltage level (or to ground for a large overdrive) for the time duration that an input is driven negative. This is not destructive and normal output states will re-establish when the input voltage, which was negative, again returns to a value greater than -0.3 VDC at 25°C).

Package/Ordering Information

MODEL	CHANNEL	ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION	MARKING INFORMATION
GS331	Single	GS331-TR	SOT23-5	Tape and Reel,3000	331





March 2020-REV_V0 2/10



Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit
Supply Voltage	V _{CC}	2	36	V
Operating Temperature Range	TA	-40	85	°C

Electrical Characteristics

VCC=5V, GND=0V, TA=25oC, unless otherwise specified. Bold typeface applies over TA=-40 to 85oC (Note 3)

Parameter	Symbol	Conditions		Min	Typ	Max	Unit
Insura Offices Voltages	Vos	V _{OUT} =1.4V, V _{CC} =5 to 30V			1	5	mV
Input Offset Voltage	VOS					7.0	mv
Innut Bire Comment	T	I _{IN} + or I _{IN} - with output in linear range,			25	250	пA
Input Bias Current	I_{B}	V _{CM} =0V	OV			400	
Input Offset Current	I _{IO}	I _{IN} +-I _{IN} -, V _{CM} =0V			5	50	nA
input Offset Current	1O			Y Y		200	
Input Common Mode Voltage Range (Note 4)		V _{CC} =30V		0		V _{CC} -1.5	V
Supply Current	3	$R_{L}=\infty$	V _{CC} =5V	Y	0.4	1.0	mA
	T					2.0	
	I_{CC}		V _{CC} =30V		0.5	1.7	
						3.0	
Voltage Gain	G_{V}	V_{CC} =15V, R_L ≥15k Ω , V_{OUT} =1 to 11V		50	200		V/mV
Large Signal Response Time		V _{IN} =TTL Logic Swing, R _L =5.1kΩ			200		ns
Response Time	5	$R_L=5.1k\Omega$			1.3		μs
Output Sink Current	I _{SINK}	V _{IN} -=1V, V _{IN} +=0V, V _{OUT} =1.5V		6.0	16		mA
Output Leakage Current	T (8)	V _{IN} -=0V, V _{IN} +=1V, V _{OUT} =5V			0.1		nA
	I _{LEAK}	V _{IN} -=0V, V _{IN} +	=1V, V _{OUT} =30V			1	μА
	17	V _{IN} -=1V, V _{IN} +=0V, I _{SINK} ≤4mA			200	400	mV
Saturation Voltage	V_{SAT}			3		500	

Note 3: These specifications are limited to -40oC≤TA≤85oC. Limits over temperature are guaranteed by design, but not tested in production.


Note 4: The input common mode voltage of either input signal voltage should not be allowed to go negatively by more than 0.3V (at 25°C). The upper end of the common mode voltage range is VCC-1.5V (at 25°C), but either or both inputs can go to 18V without damages, independent of the magnitude of the VCC.







Typical Performance characteristics







Figure 4. Supply Current vs. Supply Voltage









Figure 6. Input Offset Voltage vs. Case Temperature

Figure 7. Saturation Voltage vs. Case Temperature










800 V_∞=5V, Input Overdrive Voltage=100mV
550 Low to High
- High to Low
400
400
350
300
250
200
40 -20 0 20 40 60 80 100 120
Case Temperature (°C)

Figure 8. Saturation Voltage vs. Output Sink Current








Figure 10. Response Time vs. Load Capacitor


Figure 11. Response Time vs. Input Overdrive Voltage



March 2020-REV VO











Figure 12. Response Time vs. Supply Voltage

Figure 13. Response Time vs. Supply Voltage







Figure 14. Response Time for Positive Transition

Figure 15. Response Time for Negative Transition













Figure 16. Response Time for Positive Transition

Figure 17. Response Time for Negative Transition






Figure 18. 100kHz Response

Figure 19. 100kHz Response










Figure 20. 500kHz Response




March 2020-REV_V0





Typical Applications







Figure 21. Basic Comparator

Figure 22. Driving CMOS









Figure 24. Squarewave Oscillator






Package Information

SOT23-5





Symbol	Dimensions In Millimeters		Dimensions In Inches		
,	MIN	MAX	MIN	MAX	
Α	1.050	1.250	0.041	0.049	
A1	0.000	0.100	0.000	0.004	
A2	1.050	1.150	0.041	0.045	
b	0.300	0.500	0.012	0.020	
С	0.100	0.200	0.004	0.008	
D	2.820	3.020	0.111	0.119	
E	1.500	1.700	0.059	0.067	
E1	2.650	2.950	0.104	0.116	
e	0.950 BSC		0.037 BSC		
e1	1.900 BSC		0.075 BSC		
L	0.300	0.600	0.012	0.024	
θ	0°	8°	0°	8°	