

650V GaN Power Transistor (FET)


Features

- Easy to use, compatible with standard gate drivers
- Low Q_{rr}, no free-wheeling diode required
- Excellent Q_g x R_{DS(on)} product (FOM)
- Low switching loss
- RoHS compliant and Halogen-free

Product Summary		
V _{DSS}	650	V
R _{DS(on), typ}	230	mΩ
Q _{G, typ}	12.5	nC
Q _{RR, typ}	38	nC

Applications

- Power adapters
- Telecom and datacom
- Automotive
- Servo motors



Packaging

Part Number	Package	Packaging	Base QTY
XG65T230PS1B	3 Lead TO-220	Tube	50

Maximum ratings, at T_C=25 °C, unless otherwise specified

Symbol	Parameter		Limit Value	Unit
I _D	Continuous drain current @T _C =25°C		13	A
	Continuous drain current @T _C =100°C		8	A
I _{DM}	Pulsed drain current@T _C =25°C (pulse width: 10us)		43	A
	Pulsed drain current@T _C =150°C (pulse width: 10us)		28	A
V _{DSS}	Drain to source voltage (T _J = -55°C to 150°C)		650	V
V _{GSS}	Gate to source voltage		±20	V
P _D	Maximum power dissipation @T _C =25°C		70	W
T _C	Operating temperature	Case	-55 to 150	°C
T _J		Junction	-55 to 150	°C
T _S	Storage temperature		-55 to 150	°C
T _{CSOLD}	Soldering peak temperature		260	°C

Thermal Resistance


Symbol	Parameter	Typical	Unit
R _{θJC}	Junction-to-case	1.8	°C/W
R _{θJA}	Junction-to-ambient	50	°C/W

Electrical Parameters, at $T_J=25^\circ\text{C}$, unless otherwise specified

Symbol	Min	Typ	Max	Unit	Test Conditions
Forward Device Characteristics					
$V_{DSS-MAX}$	650	-	-	V	$V_{GS}=0V$
BV_{DSS}	-	1700	-	V	$V_{GS}=0V, I_{DSS}=250\mu\text{A}$
$V_{GS(\text{th})}$	-	1.82	-	V	$V_{DS}=V_{GS}, I_D=500\mu\text{A}$
$R_{DS(on)}^a$	-	230	270	$\text{m}\Omega$	$V_{GS}=8V, I_D=4A, T_J=25^\circ\text{C}$
	-	450	-		$V_{GS}=8V, I_D=4A, T_J=150^\circ\text{C}$
I_{DSS}	-	8	20	μA	$V_{DS}=700V, V_{GS}=0V, T_J=25^\circ\text{C}$
	-	25	-	μA	$V_{DS}=700V, V_{GS}=0V, T_J=150^\circ\text{C}$
I_{GSS}	-	-	150	nA	$V_{GS}=20V$
	-	-	-150	nA	$V_{GS}=-20V$
C_{iss}	-	490	-	pF	$V_{GS}=0V, V_{DS}=650V, f=1\text{MHz}$
C_{oss}	-	25	-	pF	
C_{rss}	-	4	-	pF	
$C_{O(er)}$	-	30	-	pF	
$C_{O(tr)}$	-	50	-	pF	$V_{GS}=0V, V_{DS}=0 \text{ to } 650V$
Q_G	-	12.5	-	nC	$V_{DS}=400V, V_{GS}=0V \text{ to } 8V, I_D=10A$
Q_{GS}	-	3	-		
Q_{GD}	-	2.8	-		
$t_{D(on)}$	-	16	-	nS	$V_{DS}=400V, V_{GS}=0V \text{ to } 12V, I_D=10A, R_G=21\Omega$
t_R	-	14	-		
$t_{D(off)}$	-	70	-		
t_F	-	7	-		
Reverse Device Characteristics					
V_{SD}	-	1.7	-	V	$V_{GS}=0V, I_S=5A, T_J=25^\circ\text{C}$
	-	2.6	-		$V_{GS}=0V, I_S=10A, T_J=25^\circ\text{C}$
	-	5	-		$V_{GS}=0V, I_S=10A, T_J=150^\circ\text{C}$
t_{RR}	-	18	-	ns	$I_S=10A, V_{GS}=0V, d_i/d_t=1200A/\mu\text{s}, V_{DD}=400V$
Q_{RR}	-	38	-	nC	

Notes:

a. Dynamic on-resistance


Circuit Implementation



Recommended gate drive: (0 V, 12 V) with $R_{G(\text{tot})} = 21 \Omega$, where $R_{G(\text{tot})} = R_{g1} + R_{\text{Driver}}$





Gate Ferrite Bead (FB)	Gate Resistance1 (Rg1)	RC Snubber (RCsn)
MMZ1608S301ATA00	20 Ω	47 pF + 15 Ω







Notes:







- a. RCsn should be placed as close as possible to the drain pin
- b. The layout and wiring of the drive circuit should be as short as possible

Typical Characteristics, at $T_c=25\text{ }^\circ\text{C}$, unless otherwise specified

Figure 1. Typical Output Characteristics $T_c=25\text{ }^\circ\text{C}$

Parameter: V_{GS}

Figure 2. Typical Output Characteristics $T_J=150\text{ }^\circ\text{C}$

Parameter: V_{GS}

Figure 3. Typical Transfer Characteristics
 $V_{DS}=10\text{V}$, Parameter: T_j

Figure 4. Normalized On-resistance
 $I_D=4\text{A}$, $V_{GS}=8\text{V}$

Figure 5. Typical Capacitance
 $V_{GS}=0\text{V}$, $f=1\text{MHz}$

Figure 6. Typical Coss Stored Energy

Typical Characteristics, at $T_c=25\text{ }^\circ\text{C}$, unless otherwise specified

Figure 7. Typical Qoss

Figure 8. Forward Characteristic of Rev. Diode
 $I_s=f(V_s)$, Parameter T_j

Figure 9. Drain-Source Breakdown Voltage

Figure 10. Typical Gate Charge
 $I_{DS}=10\text{A}, V_{DS}=400\text{V}$

Figure 11. Power Dissipation

Figure 12. Current Derating

Test Circuits and Waveforms

Figure 13. Switching Time Test Circuit

Figure 14. Switching Time Waveform

Figure 15. Dynamic $R_{DS(on)eff}$ Test Circuit

Figure 16. Dynamic $R_{DS(on)eff}$ Waveform

Figure 17. Diode Characteristic Test Circuits

Figure 18. Diode Recovery Waveform

Design Considerations

Fast switching GaN device can reduce power conversion losses, and thus enable high frequency operations. Certain PCB design rules and instructions, however, need to be followed to take full advantages of fast switching GaN devices.



Before evaluating Xinguan's GaN devices, please refer to the table below which provides some practical rules that should be followed during the evaluation.

When Evaluating Xinguan's GaN Devices:

DO	DO NOT
Make sure the traces are as short as possible for both drive and power loops to minimize parasitic inductance	Using Xinguan's devices in GDS board layouts
Use the test tool with the shortest inductive loop, and make sure test points should be placed close enough	Use differential mode probe or probe ground clip with long wires
Minimize the lead length of TO packages when installing them to PCB	Use long traces in drive circuit, or long lead length of the devices

Mechanical
3 Lead TO-220 (PS) Package

Pin 1: Gate; Pin 2: Source; Pin 3: Drain; Tab: Source


Package Outlines
Dimensions are show in millimeters

Revision History

Version	Date	Change(s)
1.0	8/3/2020	Release formal datasheet