

## 650V GaN Power Transistor (FET)


### Features

- Easy to use, compatible with standard gate drivers
- Low  $Q_{rr}$ , no free-wheeling diode required
- Excellent  $Q_g \times R_{DS(on)}$  product (FOM)
- Low switching loss
- RoHS compliant and Halogen-free

Product Summary		
$V_{DSS}$	650	V
$R_{DS(on), typ}$	120	m $\Omega$
$Q_{G, typ}$	12	nC
$Q_{RR, typ}$	80	nC

### Applications

- Power adapters
- Telecom and datacom
- Automotive
- Servo motors



### Packaging

Part Number	Package	Packaging	Base QTY
XG65T125HS1B	DFN 8*8mm	Tape and Reel	2500

### Maximum ratings, at $T_c=25^\circ\text{C}$ , unless otherwise specified

Symbol	Parameter		Limit Value	Unit
$I_D$	Continuous drain current @ $T_c=25^\circ\text{C}$		18	A
	Continuous drain current @ $T_c=100^\circ\text{C}$		11.5	A
$I_{DM}$	Pulsed drain current @ $T_c=25^\circ\text{C}$ (pulse width: 10us)		82	A
	Pulsed drain current @ $T_c=150^\circ\text{C}$ (pulse width: 10us)		62	A
$V_{DSS}$	Drain to source voltage ( $T_j = -55^\circ\text{C}$ to $150^\circ\text{C}$ )		650	V
$V_{GSS}$	Gate to source voltage		$\pm 20$	V
$P_D$	Maximum power dissipation @ $T_c=25^\circ\text{C}$		67.5	W
$T_c$	Operating temperature	Case	-55 to 150	$^\circ\text{C}$
$T_j$		Junction	-55 to 150	$^\circ\text{C}$
$T_s$	Storage temperature		-55 to 150	$^\circ\text{C}$
$T_{CSOLD}$	Soldering peak temperature		260	$^\circ\text{C}$

# XG65T125HS1B

## Thermal Resistance

Symbol	Parameter	Typical	Unit
$R_{\theta JC}$	Junction-to-case	1.85	$^{\circ}\text{C}/\text{W}$
$R_{\theta JA}$	Junction-to-ambient <sup>a</sup>	50	$^{\circ}\text{C}/\text{W}$

Notes:

- a. Device on one layer epoxy PCB for drain connection (vertical and without air stream cooling, with 6cm<sup>2</sup> copper area and 70μm thickness)


Electrical Parameters, at  $T_J=25\text{ }^\circ\text{C}$ , unless otherwise specified

Symbol	Min	Typ	Max	Unit	Test Conditions
<b>Forward Device Characteristics</b>					
$V_{DSS-MAX}$	650	-	-	V	$V_{GS}=0V$
$BV_{DSS}$	-	1700	-	V	$V_{GS}=0V, I_{DSS}=250\mu A$
$V_{GS(th)}$	-	1.82	-	V	$V_{DS}=V_{GS}, I_D=500\mu A$
$R_{DS(on)}^a$	-	120	145	m $\Omega$	$V_{GS}=8V, I_D=4A, T_J=25^\circ C$
	-	240	-		$V_{GS}=8V, I_D=4A, T_J=150^\circ C$
$I_{DSS}$	-	8	20	$\mu A$	$V_{DS}=700V, V_{GS}=0V, T_J=25^\circ C$
	-	70	-	$\mu A$	$V_{DS}=700V, V_{GS}=0V, T_J=150^\circ C$
$I_{GSS}$	-	-	150	nA	$V_{GS}=20V$
	-	-	-150	nA	$V_{GS}=-20V$
$C_{ISS}$	-	500	-	pF	$V_{GS}=0V, V_{DS}=650V, f=1MHz$
$C_{OSS}$	-	50	-	pF	
$C_{RSS}$	-	4	-	pF	
$C_{O(er)}$	-	60	-	pF	$V_{GS}=0V, V_{DS}=0\text{ to }650V$
$C_{O(tr)}$	-	100	-	pF	
$Q_G$	-	12	-	nC	$V_{DS}=400V, V_{GS}=0V\text{ to }8V, I_D=10A$
$Q_{GS}$	-	3.7	-		
$Q_{GD}$	-	2.2	-		
$t_{D(on)}$	-	24	-	nS	$V_{DS}=400V, V_{GS}=0V\text{ to }12V, I_D=10A, R_G=20\Omega$
$t_R$	-	14	-		
$t_{D(off)}$	-	100	-		
$t_F$	-	8	-		
<b>Reverse Device Characteristics</b>					
$V_{SD}$	-	1.4	-	V	$V_{GS}=0V, I_S=5A, T_J=25^\circ C$
	-	2.2	-		$V_{GS}=0V, I_S=10A, T_J=25^\circ C$
	-	3.2	-		$V_{GS}=0V, I_S=10A, T_J=150^\circ C$
$t_{RR}$	-	12	-	ns	$I_S=10A, V_{GS}=0V, di/dt=2300A/us, V_{DD}=400V$
$Q_{RR}$	-	80	-	nC	

Notes:

- a. Dynamic on-resistance; see Fig. 15 and 16 for test circuit and conditions

**Circuit Implementation**



Recommended Drive Circuit

Recommended gate drive: (0 V, 12 V) with  $R_{G(tot)} = 21 \Omega$ , where  $R_{G(tot)} = R_G + R_{Driver}$

Gate Ferrite Bead (FB)	Gate Resistance1 ( $R_G$ )	RC Snubber ( $R_{CSN}$ )
MPZ1608S471ATA00	20 $\Omega$	47 pF + 15 $\Omega$

Notes:

- RCsn should be placed as close as possible to the drain pin
- The layout and wiring of the drive circuit should be as short as possible

Typical Characteristics, at  $T_c=25^\circ\text{C}$ , unless otherwise specified




Figure 1. Typical Output Characteristics  $T_j=25^\circ\text{C}$

Parameter:  $V_{GS}$




Figure 2. Typical Output Characteristics  $T_j=150^\circ\text{C}$

Parameter:  $V_{GS}$




Figure 3. Typical Transfer Characteristics

$V_{DS}=10\text{V}$ , Parameter:  $T_j$




Figure 4. Normalized On-resistance

$I_D=4\text{A}$ ,  $V_{GS}=8\text{V}$




Figure 5. Typical Capacitance

$V_{GS}=0\text{V}$ ,  $f=1\text{MHz}$




Figure 6. Typical  $C_{OSS}$  Stored Energy

Typical Characteristics, at  $T_c=25\text{ }^\circ\text{C}$ , unless otherwise specified




Figure 7. Typical Qoss




Figure 8. Forward Characteristic of Rev. Diode

$I_s=f(V_s), \text{Parameter } T_j$




Figure 9. Drain-Source Breakdown Voltage




Figure 10. Typical Gate Charge

$I_{DS}=10A, V_{DS}=400V$




Figure 11. Power Dissipation






Figure 12. Current Derating


**Test Circuits and Waveforms**




**Figure 13. Switching Time Test Circuit**




**Figure 14. Switching Time Waveform**




**Figure 15. Dynamic  $R_{DS(on)}$  Test Circuit**



**Figure 16. Dynamic  $R_{DS(on)}$  Waveform**



**Figure 17. Diode Characteristic Test Circuit**



**Figure 22. Diode Recovery Waveform**

### Design Considerations

Fast switching GaN device can reduce power conversion losses, and thus enable high frequency operations. Certain PCB design rules and instructions, however, need to be followed to take full advantages of fast switching GaN devices.


Before evaluating Xinguan's GaN devices, please refer to the table below which provides some practical rules that should be followed during the evaluation.

**When Evaluating Xinguan's GaN Devices:**

DO	DO NOT
Make sure the traces are as short as possible for both drive and power loops to minimize parasitic inductance	Using Xinguan's devices in GDS board layouts
Use the test tool with the shortest inductive loop, and make sure test points should be placed close enough	Use differential mode probe or probe ground clip with long wires
Minimize the lead length of TO packages when installing them to PCB	Use long traces in drive circuit, or long lead length of the devices



## Mechanical




## DFN 8\*8 (HS) Package

Symbol	Dimensions in Millimeters		
	MIN	NOM	MAX
A1	1.825	1.850	1.875
A2	0.195	0.203	0.211
D	7.950	8.000	8.050
E	7.950	8.000	8.050
D1	7.150	7.200	7.250
E1	4.550	4.600	4.650
K1	0.375	0.400	0.425
K2	2.575	2.600	2.625
b1	2.275	2.300	2.325
b2	0.375	0.400	0.425
L1	0.775	0.800	0.825
L2	0.075	0.100	0.125

## Package Outlines

Dimensions are show in millimeters



## Revision History

Version	Date	Change(s)
1.0	7/30/2020	Release formal datasheet