



深圳市万瑞和电子有限公司
SHENZHEN WONDHOPE ELECTRIC CO., LTD

地址 (Add): 深圳市龙华区观澜街道观光路美泰科技园1栋
1nd Bldg, Meitai Industrial Zone, Guanguang Road,
Guanlan, Longhua, Shenzhen, China

电话 (Tel): 86-0755-29503668 29503690 29503691

传真 (Fax): 86-0755-29503998 邮编 (P.C.): 518131

邮箱 (Email): sales@whptc.com 网址 (http://): www.whptc.com

封装 (package): SMD 0603

型号 (Model): WH 035


最大电压 (V_{max}): 6 V

最大电流 (I_{max}): 40 A

产品规格书 Specification Sheet

产品标识/Marking:

II 系列标识 (Logo)




产品外形尺寸
/ Appearance
and size of
production

焊点可焊性/Solderability:

符合EIA规定RS186-9E 和ANSI/J-STD-002
第3类标准/Meets EIA specification RS186-
9E and ANSI/J-STD-002 Category 3

焊点材料/Terminal Pad Materials:

无铅镀锡的镀镍铜箔/Sn-plated nickel-copper, lead-free device.



推荐焊盘设计
/ Recommended
pad layout

产品尺寸/Dimensions:

| | A | | B | | C | | D | E | F | G | H |
|------|------|------|------|------|------|------|------|------|------|-----|------|
| UNIT | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MIN | | | |
| mm | 1.45 | 1.85 | 0.65 | 1.05 | 0.3 | 0.75 | 0.2 | 0.2 | 2.3 | 5.1 | 5.6 |
| inch | 0.06 | 0.07 | 0.03 | 0.04 | 0.01 | 0.03 | 0.01 | 0.01 | 0.09 | 0.2 | 0.22 |

电气特性/Performance Specification:

| Model | V_{max} (V _{dc}) | I_{max} (A) | I_{hold} @25°C (A) | I_{trip} @25°C (A) | P_d Typ. (W) | Maximum Time To Trip | | Resistance | |
|--------|---------------------------------|------------------|----------------------------|----------------------------|----------------------|-------------------------|---------------|--------------------------|--------------------------|
| | | | | | | Current t | Time (Sec) | R _{imin} (Ω) | R _{1max} (Ω) |
| SMD035 | 6 | 40 | 0.35 | 0.75 | 0.5 | 8.0 | 0.1 | 0.2 | 1.4 |

V_{max} : 产品在规定电流下工作不被破坏的最大电压;

/Maximum voltage, device can withstand without damage at rated current;

I_{max} : 产品在规定电压下工作不被破坏的最大电流;

/ Maximum fault current, device can withstand without damage at rated voltage;

I_{hold} : 产品在25°C静止空气中30分钟不动作的最大工作电流;

/ Hold Current, device will sustain for 30min without tripping in 25°C still air;

I_{trip} : 产品在25°C静止空气中动作的最小电流;

/ Minimum current at which the device will trip in 25°C still air;

P_d : 产品在25°C静止空气中保护状态中消耗的功率;

/ Power dissipated from device when in the tripped state in 25°C still air;

R_{imin} : 满足功能要求的最小成品电阻值;


/Minimum resistance of device in initial (un-soldered) state;

R_{1max} : 焊接完1小时, 产品在25°C静止空气中的最大电阻值。


/ Maximum resistance of device at 25°C measured one hour post reflow.

电流折减与环境温度曲线图

/Average Time Current Curve



回流焊接条件/Solder reflow conditions



注意：如果回流焊温度超过图表建议最高温度（260°C），元件可能损坏而达不到规范要求。

1、建议回流方法：红外线、蒸汽炉、热空气炉；最高温度时间越短越好，一般控制在40s以内；

/Recommended reflow methods: IR, vapor phase oven, hot air oven.

2、使用于波焊制程时，不可将元件置于电路板之背面/底面； /Devices are not designed to be wave soldered to the bottom side of the board.

3、建议焊锡膏涂抹厚度最大为0.25mm/0.010 inch； /Recommended maximum paste thickness is 0.25 mm (0.010 inch).

4、元件可使用一般业界标准程序和溶剂来实施清洁。 /Devices can be cleaned using standard method and solvents.

/Note: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

储存与放置/Storage and Handling

储存条件：低于30 °C，相对湿度小于60%。如果超出储存条件，元件可能达不到规范要求。 /Storage conditions: 30° C max, 60% R.H.Devices may not meet specified performance if storage conditions are exceeded.

订购须知/Order Information

II=系列标识（Logo），SMD0603=封装尺寸/ Packaging，035=产品型号 /Model

包装数量5000个/盘 5000pcs/Reel

注意事项/ WARNING:

- 1、超出额定范围或不正确地使用PPTC元件都可能导致产品的损坏，并可能导致电弧和火焰； /Use PPTC exceed by the maximum rating and improper use may result in device damage and possible electrical arcing and flame.
- 2、PPTC元件一般只用于偶然的过流或超温故障时的保护，切勿用于故障频繁发生或预期会发生长时间故障的场合； /PPTC are designed for protection against over current or temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- 3、如果不按照建议安装、测试和使用产品，元件性能可能会受到不利影响； /Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
- 4、在电感强度大的电路中使用，可能会产生超过PPTC元件的额定电压的回路电压； /Use PPTC with a large inductance in circuit will generate a circuit voltage above the rated voltage of the PPTC.
- 5、PPTC元件应用时不能长期处于压力下，使其缺乏膨胀空间而影响其性能，如处于高压或安装在受限的狭小空间里。 /Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
- 6、由于上述原因造成的质量问题，我司概不负责。 /If any quality problems caused by improper use mentioned above,our company is not responsible.