


VOLTAGE RANGE **50 to 1000 Volts**
CURRENT **2.0 Ampere**

FEATURES

- Plastic package has UL flammability Classification 94V-0
- Glass Passivated chip junction
- Built in strain relief
- Fast switching speed for high efficiency
- High temperature soldering guaranteed: 250°C/10 seconds

MECHANICAL DATA

- Case: JEDED DO-214AA transfer molded plastic
- Terminals: Solder plated, Solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

- Ratings at 25°C ambient temperature unless otherwise specified.
- Single phase, half wave, 60Hz, resistive or inductive load.
- For capacitive load derate current by 20%.

MAXIMUM RATINGS & THERMAL CHARACTERISTICS

PARAMETELS	SYMBOLS	US2A	US2B	US2D	US2G	US2J	US2K	US2M	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Rectified Current At $T_L=105^\circ\text{C}$ (NOTE 1)	$I_{(AV)}$	2.0							Amps
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	50							Amps
Maximum Instantaneous Forward Voltage at 2.0A	V_F	1.0		1.3		1.7		Volts	
Maximum DC Reverse Current At rated DC blocking voltage at	$T_A=25^\circ\text{C}$	5.0							μA
	$T_A=125^\circ\text{C}$	100							
Maximum Reverse Recovery Time Test conditions $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{RR}=0.25\text{A}$	t_{rr}	50				75			nS
Typical Junction Capacitance (Measured at 1.0MHz and applied reverse voltage of 4.0V)	C_J	50				30			pF
Typical Thermal Resistance (NOTE 1)	$R_{\theta JA}$	75							$^\circ\text{C/W}$
	$R_{\theta JL}$	17							
Operating Junction Temperature	T_J	(-55 to +150)							$^\circ\text{C}$
Storage Temperature Rang	T_{STG}	(-55 to +150)							$^\circ\text{C}$

Notes:

1. Thermal resistance from Junction to ambient and from junction to lead mounted on P.C.B. with 0.3×0.3" (8.0 × 8.0mm) copper pad areas.

RATING AND CHARACTERISTIC CURVES

FIG. 1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 4-TYPICAL REVERSE CHARACTERISTICS




FIG. 5-TYPICAL JUNCTION CAPACITANCE




FIG. 6-TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC

