



B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND
PIN	SIGNAL NAME

- NOTES:
- MATERIAL:
 - MOLDING: LCP UL94 V-0
 - CONTACT: COPPER ALLOY.
 - Finished: contact area: plating Au 0.8u", solder tail: plating Au 0.8u", all plating Ni 40u" SHELL: SUS201-1/2H, T=0.30±0.03mm 50u" NICKEL PLATING OVER ALL.
 - MECHANICAL:
 - INSERTION: 5~20N.
 - EXTRACTION: 8~20N AFTER TEST.
 - DURABILITY: 8000 CYCLES
 - ELECTRICAL:
 - CURRENT: 5A FOR VBUS; 1.25A FOR GND PIN. 0.25A FOR OTHER.
 - VOLTAGE: 20 V MAX
 - WITHSTANDING VOLTAGE: 100V AC R.M.S.
 - CONTACT RESISTANCE: 40mΩ MAX.
 - INSULATION RESISTANCE: 100MΩ MIN.
 - ENVIRONMENTAL
 - TEMPERATURE RANGE -25°C ~ +85°C

U262-06XN-4BVC11

1: 0.8u"
2: 5u"
3: 10u"

					DSND		DATE		SCALE: N/A	MODEL TYPE:	3.1 TYPE C			
ΔX					ANGLAR		DATE		VIEW:	PART NO.:				
ΔX					L ≤ 4	±0.2	CHKD		UNIT: mm	DWG NO.:				
ΔX					4 < L ≤ 16	±0.3	APPD		SIZE: A4	U262-06XN-4BVC11	WEIGHT	SHEET	REVISION	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4					1.0g	1/1	A0	
					L > 63	±0.5					XKB INDUSTRIAL PRECISION CO., LIMITED			
REVISIONS					UNSPECIFIED TOLERANCES									
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														