






MAPX	MODIFICATION	DATE



TOLERANCE: ± 0.05 ,
RECOMMENDED PCB LAYOUT
(TOP VIEW)

NOTES:

- 1.MATERIAL:
 1.1 HOUSING: HIGH TEMPERATURE THERAL PLASTIC.
 1.2 SPRING CONTACT: COPPER ALLOY.
 1.3 FLAT CONTACT;COPPER ALLOY
 1.4 SHELL :COPPER ALLOY.
 1.5 COVER:HIGIH TEMPERATURATURE THERAL PLASTIC.
- 2.FINISH:
 2.1 CONTACT: (SEE P/N.),[50 μ "] MIN. NICKEL UNDERPLATING OVER ALL.
 2.2 SHELL: [50 μ "] MIN.SOLDERABLITY NICKEL UNDERPLATING OVER ALL.



PIN NO.	PIN 1	PIN 2	PIN 3	PIN 4
SLGNL NAME	V BUS	D-	D+	GND
REMARK	USB 2.0 CONTACT PINS			

PIN NO.	PIN 5	PIN 6	PIN 7	PIN 8	PIN 9
SLGNL NAME	STDA_SSRX-	STDA_SSRX+	GND_DRAIN	STDA_SSTX-	STDA_SSTX+
REMARK	USB 3.0 CONTACT PINS				

产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司							
公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	尹先华	制图料号 PRODUCT PART NO.	916-152A2058Y20201		
X.	± 0.25	X.	$\pm 5^\circ$	比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	AF3.0 180度15.0直脚无边铜壳LCP蓝色
.X	± 0.20	.X	$\pm 2^\circ$	日期 DATE	2021-04-14	核准 APPD	黄国荣	角法 VIEW	版本 VER
.XX	± 0.15	.XX	$\pm 1^\circ$						AO
.XXX	± 0.10	.XXX	$\pm 0.5^\circ$						