



MAPX	MODIFICATION	DATE



TOLERANCE: ± 0.05
 RECOMMENDED PCB LAYOUT
 (TOP VIEW)





NOTES:

1.MATERIAL:

- 1.1 HOUSING: HIGH TEMPERATURE THERAL PLASTIC.
- 1.2 SPRING CONTACT: COPPER ALLOY.
- 1.3 FLAT CONTACT;COPPER ALLOY
- 1.4 SHELL :COPPER ALLOY.
- 1.5 COVER:HIGIH TEMPERATURATURE THERAL PLASTIC.

2.FINISH:

- 2.1 CONTACT: (SEE P/N.),[50 μ] MIN. NICKEL UNDERPLATING OVER ALL.
- 2.2 SHELL: [50 μ] MIN.SOLDERABILITY NICKEL UNDERPLATING OVER ALL.



PIN NO.	PIN 1	PIN 2	PIN 3	PIN 4
SLGNL NAME	V BUS	D-	D+	GND
REMARK	USB 2.0 CONTACT PINS			

PIN NO.	PIN 5	PIN 6	PIN 7	PIN 8	PIN 9
SLGNL NAME	STDA_SSRX-	STDA_SSRX+	GND_DRAIN	STDA_SSTX-	STDA_SSTX+
REMARK	USB 3.0 CONTACT PINS				

产品图 PRODUCT CHART DWG		<h1 style="margin: 0;">深圳市精拓金电子有限公司</h1>							
公差一览表 TOLERANCE UNLESS OTHERWISE		单位	MM	制图	尹先华	制图料号	916-262A101DY20400		
X.	± 0.25	X.	$\pm 5.^\circ$	比例	郭治富	产品名称	AF3.0/180度15.0直脚有边铜壳LCP蓝色		
.X	± 0.20	.X	$\pm 2.^\circ$	日期	黄国荣	角法	版本 VER		
.XX	± 0.15	.XX	$\pm 1.^\circ$	日期	2021-04-14	核淮	AO		
.XXX	± 0.10	.XXX	$\pm 0.5^\circ$	APPD					