

FEATURES

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- Ideally suited for use in very high frequency switching power supplies, inverters and as a free wheeling diode
- Ultrafast recovery time for high efficiency
- Soft recovery characteristics
- Excellent high temperature switching
- Glass passivated junction
- High temperature soldering guaranteed: 250°C/10 seconds, 0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension

Mechanical Data


Case: JEDEC DO-214AC, molded plastic body over passivated chip

Terminals: Axial leads, solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.012 ounce, 0.34 gram



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

Characteristic	Symbol	US1A	US1B	US1D	US1G	US1J	US1K	US1M	Unit	
Peak Repetitive Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V	
Working Peak Reverse Voltage	V_{RWM}									
DC Blocking Voltage	V_R									
RMS Reverse Voltage	$V_{R(RMS)}$	35	70	140	280	420	560	700	V	
Average Rectified Output Current @ $T_T = 75^\circ\text{C}$	I_O	1.0								A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave Superimposed on Rated Load (JEDEC Method)	I_{FSM}	30								A
Forward Voltage Drop @ $I_F = 1.0\text{A}$	V_{FM}	1.0			1.3	1.7			V	
Peak Reverse Current @ $T_A = 25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_A = 100^\circ\text{C}$	I_{RM}					5.0	100			μA
Reverse Recovery Time (Note 2)	t_{rr}	50				75			ns	
Typical Junction Capacitance (Note 1)	C_j	20				10			pF	
Typical Thermal Resistance, Junction to Terminal	$R_{\theta JT}$	30							$^\circ\text{C/W}$	
Operating and Storage Temperature Range	T_j, T_{STG}	-65 to +150							$^\circ\text{C}$	

- Notes: 1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
2. Measured with $I_F = 0.5\text{A}$, $I_R = 1.0\text{A}$, $I_{rr} = 0.25\text{A}$.

FIG. 1 - FORWARD CURRENT DERATING CURVES




FIG. 2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 3 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG. 4 - TYPICAL REVERSE CHARACTERISTICS




FIG. 5 - REVERSE SWITCHING CHARACTERISTICS





FIG. 6 - TYPICAL JUNCTION CAPACITANCE



ORDERING INFORMATION

Order Code	Package	Baseqty	Deliverymode
UMW US1A	SMA	2000	Tape and reel
UMW US1B	SMA	2000	Tape and reel
UMW US1D	SMA	2000	Tape and reel
UMW US1G	SMA	2000	Tape and reel
UMW US1J	SMA	2000	Tape and reel
UMW US1K	SMA	2000	Tape and reel
UMW US1M	SMA	2000	Tape and reel