

Transient Voltage Suppressor

Draft Version:X0 2020-11-26

Features

- IEC 61000-4-2 (ESD) $\pm 15KV$ (air), $\pm 15KV$ (contact)
- IEC61000-4-4(EFT): 40A (5/50ns)
- IEC61000-4-5(surge): 4A (8/20 μ s)
- 32Watts peak pulse power (tp=8/20 μ s)
- Low capacitance: 0.4pF (Typical)
- Small package: DFN0603-2L


Exterior


Application Information

- USB 2.0 and USB 3.0
- HDMI 1.3, HDMI 1.4 and HDMI 2.0
- SATA and eSATA interface
- IEEE 1394
- Portable Electronics and Notebooks

Package (top view) DFN0603-2L

Agency Approvals

Icon	Description
RoHS	Compliance with 2011/65/EU
HF	Compliance with IEC61249-2-21:2003
	Mean lead free

Schematic(top view)

Part Number and Electrical Parameter

Part Number	$I_{DRM}@V_{DRM}$		$V_{BR}^{①}@I_R$		$V_c@I_{pp}^{②}$		$V_c@I_{pp}^{②}$	
	μA	V	V	mA	V	A	V	A
BV-F603UCD	MAX		MIN		MAX		MAX	
	0.1	3.3	7.0	1.0	5.5	1	8	4
	$CO^{③}$		$R_{DYN}@TLP^{④}$		$V_c@I_{pp} TLP^{④}$		ESD Contact mode ^⑤	
	pF		Ω		V	A	V	KV
	TYP	MAX	TYP		TYP		TYP	
	0.4	0.55	0.3		9	16	9	8

Absolute maximum ratings measured at T= 25°C RH = 45%-75% (unless otherwise noted).

 ① I_{DRM} is measured at $V_{DRM}=12V$; V_{BR} is measured at $I_R=1mA$; V_{SB} is measured at $I_{SB}=50mA$

 ② Surge Waveform: 8/20 μ s, pin 1 to pin2 and pin2 to pin1

 ③ Off-state capacitance is measured in $V_{DC}=0V$, f=1MHz

 ④ TLP parameter: $Z_0 = 50\Omega$, $t_p = 100ns$, $t_r = 2ns$, R_{DYN} is calculated from 4A to 16A.

⑤ Contact discharge mode, according to IEC61000-4-2.

Transient Voltage Suppressor

Mark

Draft Version:X0 2020-11-26


BV F6 03 U C D
(1) (2) (3) (4) (5) (6)

- (1) Bencent Transient Voltage Suppressor
- (2) Package:DFN0603-2L
- (3) Off-state Voltage: 3.3V
- (4) Low Capacitance
- (5) Bi-directional
- (6) Bencent intenal code








V-I Curve

Parameters	Definition
V_C	Clamping voltage
I_{PP}	Surge waveform 8/20 μ s
V_{DRM}	Stand-off Voltage
V_{BR}	Breakdown Voltage
I_{DRM}	Reverse Leakage Current
I_R	Test current
V_{SB}	Snapback Voltage
I_{SB}	Test current
P_{PP}	Peak Pulse Power Dissipation




Typical Characteristics





ESD clamping
(+8kV contact discharge per IEC61000-4-2)



ESD clamping
(-8kV contact discharge per IEC61000-4-2)

Thermal Considerations

symbol	Parameter	Value	Unit
T _J	Operating Junction Temperature Range	-55 to +125	°C
T _S	Storage Temperature Range	-55 to +150	°C


Environmental Characteristics

Testing items	Technical standards
High temperature Reverse Bias Test	Temperature: 150±3°C Bias=80%V _{DRM} Time: 168H
High Temperature Life Test	Temperature: 150°C Time: 168H
High-low Temperature Cycle test	Temperature: From -55°C to 150°C Dwell time: 30min, 100cycles
High Temperature & High Humidity Test	Temperature: 85°C Humidity: 85% Time: 168H
Pressure cooker Test	Temperature: 121°C, 2atm. Humidity: 100% Time: 24H
Resistance of soldering heat	Temperature: 260±5°C Time of dip soldering: 10s, 3times

Note: The above testing items can be specified by customer's special request


Transient Voltage Suppressor
Product Dimensions

Draft Version:X0 2020-11-26



REF	mm	inch
A	0.23~0.35	0.009~0.014
A1	0.00~0.05	0.000~0.002
A3	0.102REF	0.004REF
D	0.55~0.67	0.022~0.026
E	0.25~0.37	0.010~0.015
L	0.10~0.20	0.004~0.008
e	0.40BSC	0.016BSC
b	0.20~0.30	0.008~0.012

Recommended Soldering Pad




Notes:

This recommended land pattern is for reference purposes only. Please consult your manufacturing group to ensure your PCB design guidelines are met


Transient Voltage Suppressor

Draft Version:X0 2020-11-26

Reflow Condition		Pb-Free assembly
Pre Heat	Temperature Min	150°C
	Temperature Max	200°C
	Time (min to max)	60 – 180 secs
Average ramp up rate (Liquid) T _{amp} (T _L) to peak		3°C/s max
T _S (max) to T _L - Ramp-up Rate		3°C/s max
Reflow	- Temperature (T _L) (Liquid)	217°C
	- Temperature (T _L)	60 – 150 secs
Peak Temperature (T _P)		260+0/-5 °C
Time within 5°C of actual peak Temperature (T _P)		30secs
Ramp-down Rate		6°C/s max
Time 25°C to peak Temperature (T _P)		8 mins max.
Do not exceed		260°C



Package Reel Information



REF	mm	inch
A	0.40+/-0.05	0.016+/-0.002
B	0.70+/-0.05	0.028+/-0.002
d	1.50+0.1/-0	0.059+0.004/-0
D	178.00+/-2.00	7.008+/-0.079
D1	55.00+/-3.00	2.165+/-0.118
D2	13.00+/-0.50	0.512+/-0.020
E	1.75+/-0.10	0.069+/-0.004
F	3.50+/-0.20	0.138+/-0.008
P	2.00+/-0.20	0.079+/-0.008
P0	4.00+/-0.20	0.157+/-0.008
P1	2.00+/-0.20	0.079+/-0.008
W	8.00+/-0.20	0.315+/-0.008
W1	9.50+/-1.00	0.374+/-0.039

OUTLINE	REEL (PCS)	PER CARTON (PCS)	REEL DIAMETERS (mm)	CARTON SIZE(mm)		
				L	W	H
TAPING	10,000	300,000	178	390	370	220