



REFERENCE SPECIFICATION

Customer: JUDE		
Item:	Simple Packaged Crystal Oscillator (SPXO)	
Туре:	NZ2520SH	
Nominal Frequency:	24 MHz	For your reference we submit this specification.
Customer's Spec. No.:		Please study and keep in your related document file.
NDK Spec. No.:	ERG5007B	

		R	Revision Record			
Rev.	Date	Items	Contents	Approved	Checked	Drawn
	24.Sep.2015	Issue		Y.Akasaka		T.Wada
Α	9.Oct.2015	3.Type	Change	Y.Akasaka		C.Sakurai
		5.7 Operating Temperature Range	-40 to +85 °C→-40 to +105 °C			
В	24.Oct.2018	5.8 Overall Frequency Tolerance	Add (+/-50ppm at -40 to +105 °C)	Y.Akasaka	H.Okajima	C.Sakurai
D	24.001.2016	8.1 Dimension drawing	EKD14B-00027(Rev. C→Rev. E)	r.Akasaka	п.Окајіпа	C.Sakurai
		8.2 Marking drawing	EKH11B-00052(Rev. H→Rev. K)			
		8.3 Reliability assurance Item	EKS30B-00060(Rev. C→Rev. E)			
		5.7 Operating Temperature Range	-40 to +105 °C →-40 to +125 °C			
С	8.Oct.2019	5.8 Overall Frequency Tolerance	Add (+/-80ppm at -40 to +125°C)	Y.Akasaka		R.Saito
	0.000.2010	8.1 Dimension drawing	EKD14B-00027(Rev. E→Rev. F)			

1. Customer's Spec. No. : -----

2. NDK Spec. No. : ERG5007B

3. Type : NZ2520SH

4. Maximum Ratings


	Itama		Ratings	Notes	
	ltem	min	max	Units	Notes
1	Supply Voltage	-0.3	4.0	V	
2	Storage Temperature Range	-55	+125	°C	


5. Electrical Specifications

(Unless otherwise noted, TA=-40 to +125 °C, V_{CC}=1.8 V, Load=15 pF)

	Dawanastana		1.0 1, 20	Electric	Notes				
	Parameters	SYM	min	typ	max	Units	- Notes		
1	Nominal Frequency	f _{nom}		24		MHz			
2	Supply Voltage	Vcc	1.62	1.8	1.98	V			
3	Current Consumption (Operating)	Icc			4.0	mA	at 25°C		
4	Current Consumption (Stand-by)	I _{ST}			20	μΑ	at 25°C		
5	Output Level	-		C-N	10S				
6	Load Capacitance	C∟			15	pF			
7	Operating Temperature Range	T _{opr}	-40		+125	°C			
		Δf/f _{nom}	-20		+20	ppm	at -30 to +75 °C*1		
8	Overall Frequency Tolerance		-30		+30	ppm	at -40 to +85 °C*1		
°			-50		+50	ppm	at -40 to +105 °C*1		
			-80		+80	ppm	at -40 to +125 °C*1		
9	Output Voltage	V _{OL}			0.1 V _{CC}	V			
9	Output voltage	V _{OH}	$0.9 V_{CC}$			V			
10	Rise Time(t _r), Fall Time(t _f)	t _r /t _f			6	ns	0.1 V _{CC} to 0.9 V _{CC}		
11	Symmetry	SYM	45		55	%	at 1/2 V _{CC}		
12	Start-up Time	t _{su}			4	ms			
13	Output Wave Form	-		Rectangular					
	Stand-by Function								
14	#1 PAD input		# 3 PAD output						
'-	H level (0.7 V_{CC} to V_{CC}) or open	Operating							
	L level (0.3 V _{CC} max)		High impedance						

^{*1} Inclusive of Freq. tolerance (at 25 °C), frequency/temperature characteristics, frequency/voltage coefficient.





CL; 15pF MAX including input capacity of oscilloscope

Cby; Bypass capacitor (0.01uF)

7. Test data will not be submitted.

8. Application drawing

8.1 Dimension drawing

EKD14B-00027

8.2 Marking drawing

EKH11B-00052

8.3 Reliability assurance Item

EKS30B-00060

8.4 Taping & Reel drawing

EKK17B-00032

EEK17B-00015

9. Instruction Notice

9.1 Noise

When the NZ2520 series are used, the 0.01 μ F capacitor should be connected between V_{CC} and GND line. (Closer to the product terminal is desirable.)

9.2 Resistance to dropping

The NZ2520 series is designed to be impactproof so that no damage occurs when dropped a height(75 cm) three times. However, if dropped from a desk etc., it is advisable to check their performance or contact us to check it.

9.3 Electrostatic protection

The NZ2520 series employ C-MOS ICs for the active element. Please use them in static-free environments.

9.4 High temperature

Normal operation cannot be guaranteed for the NZ2520 series at +125 °C (for 24 hours). Be sure that the units are kept within the specified temperature range.

9.5 Cleaning

Basically, the NZ2520 series are applicable for ultrasonic wave cleaning. However, in some case, during ultrasonic wave cleanings, internal design may get damage. Please check condition carefully beforehand.

9.6 Other

The NZ2520 series are C-MOS applied products. And careful handling(same as with C-MOS IC) are needed to avoid electrostatic problems.


Incorrect PAD connection is cause of trouble. Please make sure to connect correctly as below.


#2 terminal → GND

#4 terminal \rightarrow V_{CC}

10. Order items are manufactured according to specification. As to conditions, which are not indicated in this specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.


*Example For Soldering Conditions (The below graph corresponds to Pb free solder)






	Dat	e of Revise	Charge	Approved	ed Reason				
F	19	.Sep.2019	C.Sakurai	Y.Akasaka	Add Land pattern (Recommended)				
	Date		Name	Third Angle Proj	ection	ction Tolerance		e Scale	
Draw	'n	23.Oct.2003	M.Yamaguchi	Dimension : r	mm				
Desi	gned	27.Jun.2003	M.Yamaguchi	Title			Drawing No.		Rev.
Che	cked			NZ25	NZ2520S		FKD44B 00027		F
Appr	roved	23.Oct.2003	H.Omata	Dimension of External		EKD14B-00027		F	

NIHON DEMPA KOGYO CO., LTD.




*1 [FREQUENCY]

Digits are five and 6TH digit will be omitted. MHz unit sign is not marked. ex,) $28.63636MHz \rightarrow 28.636$ [Unit sign not marked]



*3 [WEEK CODE (Digit are three)]

ex1,) In case of 7TH week of 2006



[MODEL MARK]		
NZ2520SA →	Space	
NZ2520SB \rightarrow	В	
NZ2520SC →	С	
NZ2520SD \rightarrow	D	
NZ2520SDA→	D	
NZ2520SEA→	Ε	
NZ2520SEB→	Ε	
NZ2520SF \rightarrow	F	
NZ2520SG →	G	
NZ2520SH →	Н	
NZ2520SHA→	Н	
NZ2520SHB→	Н	
NZ2520SHC→	Н	
NZ2520SJ →	J	

ex2,) In case of 31^{TH} week of 2006

6 3 1

*4 [Trace code]

Trace code consists of four digits number or letter.

This code indicates production date and production line number.

	Date of Revise Charge Ap		Approved	Reason					
K	K 12.Apr.2018 Y.Okajima		Y.Okajima	S.Murase	Model mark addition.(NZ2520SHB,SHC)				
Date		Date	Name	Third Angle Projection		Tolerance	Scale		
Dra	wn	27.Jan.2006	Y.Oishi	mm					
Des	signed	27.Jan.2006	Y.Okajima	Title			Drawing No.		Rev.
Che	ecked	27.Jan.2006	C.Ishimaru				EKH11B-00052		k
Арр	roved	27.Jan.2006	H.Omata	NZ2520S Marking			LKIIIID.	-00032	rx


Environmental Test Conditions	Specification
1.Thermal Shock Test	
1 cycle: -40°C (30 minutes) ~ +85°C(30 minutes)	*1
Number of cycle: 100 cycle.	
2.High Temperature High Humidity Test	
Temperature : +85°C, Humidity : 80 ~ 85%,	*1
Time: 250 hours.	
3.+85°C Aging (Non Operating)	*1
Temperature: +85°C, Time: 500 Hours.	*
4. Vibration Test	
MIL-STD-202F test method:204D	
Test condition : D	*1
10 ~ 2000Hz, 1.52mmp-p, or 196m/s ²	
20 minutes/cycle, XYZ 3 directions 4 times.	
5.Shock Test	
MIL-STD-202F test method : 213B	*1
Test condition : Half sinusoidal wave	71
29400m/s², 0.3ms, 3 directions, 3 times each.	
6. Drop Test (JIG attachment)	
Dummy load: 200g, Height: 1.5m,	
Fall conditions : On concrete	*1
The number of times of fall : Six directions and 1 time each are	•
made into 1 cycle, and it is	
10 cycle.	More than 90% of
7.Soldering Test (Reflow)	should be covered
Pre heat : 150±10°C, 60~120sec.	
Main heat : 30±1 seconds after amounting to 215 °C.	by solder.
Peak temperature : 240°C	
8.Soldering Resistance (Reflow)	
Pre heat : 180±10°C, 120 sec min,	
Main heat : 225°C min, 70sec max.	*1
Peak temperature: 260°C.	
Reflow time: 3 times.	(' f ' 1

^{*1} After the test mentioned above, the electrical specifications are satisfied. Also frequency deviation before and after test should be


≦ΔF/F ±10×10⁻⁶

The electrical specifications are I_{CC} , Tr/Tf, V_{OL}/V_{OH} , duty cycle, stand-by current consumption.

Document No. EKS11B-01799C 8/9



	Da	te of Revise	Charge	Approved	Reaso	n			
С	5	.Sep.2012	Y.Oishi	C.Ishimaru	C.Ishimaru 3000pcs-Product Tape→300		uct Tape→3000p	cs MAX-Prod	luct Tape.
		Date	Name	Third Angle Projection Tole		Tolerance Scal		ale	
Draw	vn	7.Oct.2003	Y.Okajima	Dimension:mi	m			1	
Desi	igned	7.Oct.2003	Y.Okajima	Title			Drawing No.		Rev.
Che	cked			NZ2520		EKK17B-00032			
Аррі	Approved 7.Oct.200		H.Omata	Taping and F	Reel S	pec.	ENNI/D-	-00032	C



	Dat	te of Revise	Charge	Approved	proved Reason					
С	4	Jul. 2012	H.Ohkubo	K.Oguri	Addition of condition when reels are 1 to 4.			to 4.		
Date		Name	Third Angle Proje	ection Tolerance		olerance Scale				
Drav	wn	26 Feb. 2010	10 H. Ohkubo Dimension:r		m					
Des	Designed 26 Feb. 2010		K.Oguri	Title			Drawing No.		Rev.	
Che	ecked	26 Feb. 2010	K.Oguri	180 dia. Reel package		EEK17B-	00045			
Approved		26 Feb. 2010	J. Nakamura	180 dia. Reel packa		aye	EEKI/D.	-00015	С	

NIHON DEMPA KOGYO CO., LTD.