				Rol				
MESSRS:			APPROVAL NO	747-00				
			DATE	2015.01.				
	AL	UMINUM ELECTROLY	TIC					
	<u>C</u>	<u>A P A C I T O</u>	<u>R</u>					
	APPR	OVAL S	HEET					
	CATALOG TYPE	KMG S	ERIES]				
	USER PART NO.							
	适用机种							
	特记事项	特记事项 Halogen-Free						
USER APP	PROVAL:							
		APPR	OVAL NO.:					

APPROVAL NO.

747-009

ALUMINUM ELECTROLYTIC CAPACITOR

PAGE: 1 OF 5

Specifications of KMG Series

ltem	Characteristics														
Rated Voltage Range	6.3 ~ 100V _{DC} 160 ~ 400V _{DC} 450V _{DC}														
Operating Temperature Range	- 55 ~ + 105 ℃ - 40 ~ + 105 ℃										- 25 ~ + 105 ℃				
Capacitance Tolerance	±20% <m> (at 20℃, 120F</m>												łz)		
	The following specificatio	ns shall	be satist	fied whe	n the ra	ted v	voltage	is appl	ied for tl	ne require	ed time				
	<	≤100V _D	С							>100\	/ _{DC}				
Leakage Current (max.)	After 1 minute:0.03CV(µA														
(at 20 ℃)	After 2 minutes:0.01CV(µA) or 3 µA,whichever is greater								minute	9	After 5 r	ninutes			
(4.20 0)	Where, C = Nominal capa	<i>,</i> .					CRVF	ุ่≼1000	CrVr>	1000 C	00 CRVR≤1000 CRVR>1000				
	V = Rated Volta		(۳)				0.1C	RV _R +40	0.04C _R \	/ _R +100 0.0	03C _R V _R +15	0.02C _R V _R +	25		
Dissipation Factor (TANō)	Rated Voltage(VDC)	6.3	10	16	25		35	50	63	100	160~250	350~450	D		
(20℃,120Hz)	TANδ (Max)	0.34	0.24	0.20	0.16	; ,	0.14	0.12	0.10	0.09	0.20	0.24			
	When the capacitance				www										
	Rated Voltage(VDC)	6.3	10	16	25	35	50	0 63	~160	200~250	350~400	450			
Temperature Characteristics	Z-25℃/Z20℃	5	4	3	2	2	2	2	3	3	6	6			
(Impedance ratio at 120Hz)	Z-40 ℃/ Z20 ℃	12	10	8	5	4	3	;	4	5	6	-			
	The following specificatio	ns shall	be satis	fied whe	n the ca	apac	itors ar	re restor	red to 20)℃ after t	he rated				
	voltage applied for 2,000 hours at 105 $^\circ$ C. (where,1000 hours $\leq 8\Phi$)														
Load Life	Capacitance change: $\leq \pm 20\%$ of the initial value														
	Tanδ	≤200%	≶200% of the initial specified value												
	LC		nitial spe												
	The following specificatio				n the ca	apac	itors ar	re restor	red to 20	C after e	exposing the	em			
	for 1,000 hours at 105℃ The rated voltage shall be		•	•••	s for a i	ninir	ninimum of 30 minutes,at least 24 hours and not more								
	•	•••		•					atoo,at						
Shelf Life	than 48 hours before the measurements.(where , 500 hours $\leq 8\Phi$) Capacitance change: $\leq \pm 20\%$ of the initial value														
	Tano $\leq 200\%$ of the initial specified value														
	LC \leq The initial specified value (Where, 200% for \geq WV 160V _{DC})														
Others	Satisfied characteristics	KS C IEC	60384-	4											
A. DIAGRAM OF DIM	ENSION				B	M	ARKI	NG: <u>B</u>	ROW	SLEE	VE, <u>WHIT</u>	<u>e</u> ink			
$ \begin{array}{c} $															
When $\Phi D \leq 8, \circ$	$D' \leq \Phi D$ +0.5,and L' \leq L				İ	RO	NT VIE	W OF (CAPACI	TO BAG	CK VIEW O	F CAPAC	ITOR		
When $\Phi D > 8, \phi$	$D' \leq \Phi D$ +0.5,and L' \leq L	.+2.0				Γ	←		*	_	+	_			
Φ D 5 6.3 Φ d 0.5 0.5 F 2 2.5			李波		立波	ē)	阿勇								

ALUMINUM ELECTROLYTIC CAPACITOR

APPROVAL NO. 747-009

RATINGS OF KMG SERIES

CAP	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450
0.1						5X11	5X11 3.2	5X11 3.6						
0.22						<u>2.1</u> 5X11	5X11	5X11						
0.33						3.2 5X11	4.3 5X11	4.8 5X11						
						6.3 5X11	7.2 5X11	7.8 5X11	6.3X11	6.3X11	6.3X11	6.3X11		
0.47						10	11 5X11	12	12 6.3X11	12 6.3X11	12 6.3X11	12 6.3X11		
0.68						5X11 12	13	5X11 14	14	15	15	15		
1						5X11 13	5X11 15	5X11 16	6.3X11 16	6.3X11 17	6.3X11 17	6.3X11 18	6.3X11 19	8x11.5 16
2.2						5X11 18	5X11 19	5X11 21	6.3X11 22	6.3X11 24	6.3X11 27	8X11.5 29	8X11.5 30	10X12.5 28
3.3						5X11	5X11	5X11	6.3X11	6.3X11	8X11.5	8X11.5	10X12.5	10X16
				5X11	5X11	30 5X11	33 5X11	34 5X11	35 6.3X11	36 8X11.5	37 8X11.5	38 10X12.5	41 10X16	38 10X20
4.7				25	27	37	39	40	41	42	45	47	49 8x11.5	45
	-												39	101/10
6.8														10X16 54
0.0				5X11 31	5X11 33	5X11 44	5X11 48	5X11 49	8X11.5 52	10X12.5 59	10X12.5 60	10X16 62	10X16 65	10X20 59
10			5X11 35	5X11 37	5X11 40	5X11 54	5X11 59	6.3X11 61		10X12.5 72	10X16 74	10X20 79	10X20 86	12.5X20 84
				- 37		04	- 39	01	11	12	/4	19	12.5X20	04
22		5X11	5X11	5X11	5X11	5X11	5X11	6.3X11	10X20	10X20	10X20	12.5X20		16X25
		48	53	56	67	79	87	100	117	119	127	150	163 12.5X30	151
33	51/4.4	51/14	EX44	5244	51/14	51/44	0.01/14	0)(11 5	40)/00	402/00	10 51/00	402/05	221	10/04 5
	5X11 52	5X11 56	5X11 60	5X11 75	5X11 80	5X11 97	6.3X11 122	8X11.5 144	10X20 156	10X20 158	12.5X20 184	16X25 200	16X25 222	16X31.5 203
17													16X20 250	16X35.5 254
47	5X11 61	5X11 66	5X11 77	5X11 80	5X11 101	6.3X11 133	6.3X11 146	10X12.5 199	12.5X20 218	12.5X20 220	12.5X25 238	16X25 265	16X31.5 290	18X25 190
	5X11	5X11	5X11	5X11	6.3X11	8X11.5	8X11.5	10X16	12.5X25	16X20	16X25	16X31.5	18X35.5	18X31.5
68	69	83	92	113	138	189	207	264	287	293	318	348	392 18X20	235
													290	18X31.5
82							0)(11.5							254
100							8X11.5 235							
100	5X11 90	5X11 100	5X11 125	6.3X11 159	6.3X11 168	8X11.5 229	10X12.5 251	10X20 349	12.5X25 360	16X25 386	16X31.5 422	18X31.5 450		
120						-				12.5X35 440				
										16X31.5				
220	5X11	5X11	6.3X11	8X11.5	8X11.5	10X12.5	10X16	12.5X25	16X31.5	684 18X35.5	18X40			
	153 6.3X11	170 6.3X11	213 8X11.5	277 8X11.5	294 10X12.5	395 10X16	474 10X20	662 16X20	680 18X35.5	705	730			
330	216	239	308	340	419	529	633	810	863					
470	6.3X11 258	6.3X11 286	8X11.5 366	10X12.5 471	10X16 547	10X20 690	12.5X20 886	16X25 1072						
470					10X20 547									
680	8X11.5		10X12.5		12.5X16		12.5X25							
1000	365 8X11.5	472 10X12.5	480 10X16	620 10X20		973 12.5X25		1410 18X40						
	443	571	680	821 12.5X20	1023 16X20	1287	1565	2020						
2200	10X20	10X20	12 5820	1160 12.5X25	1394 16X25	16X35.5								
	817	886	1108	1297	1497	1884								
3300	10X20 1032	12.5X20 1205	12.5X25 1389	16X25 1646	16X35.5 1950	18X35.5 2260	↓		ZE ØD X <u>ble Ripple</u>		(mArms/1	<u>05℃,</u> 120	Hz)	
4700		12.5X25 1492	16X25 1740		18X35.5 2335									
6800	12.5X25	16X25	16X31.5	18X35.5	2000							<u> </u>		
10000	1554 16X25	1824 16X35.5	2081 18X35.5	2452										
	1897 16X35.5	2201 18X35.5	2527											
15000	2344	2606												

SamYoung Electronics Co., Ltd.


PAGE: 2 OF 5


PAGE: 3 OF 5

ALUMINUM ELECTROLYTIC CAPACITORS

APPROVAL NO. 747-009

STRUCTURE AND MATERIALS





CE04 TYPE

MINIATURE SIZED TYPE CAPACITORS COMPONENT

MATERIALS	VENDER						
	KISTRON	(KOREA/CHINA)					
TINNED COPPER - PLY WIRE(Pb-FREE)	КОНОКИ	(JAPAN/CHINA)					
	NANTONG HONG YANG	(CHINA)					
	KANG WON AUTO FITTING						
	NAN TONG HUI FENG	(CHINA)					
ALUMINUM 99.92 % OVER	NANTONG HONG YANG						
	КОНОКИ	(JAPAN/CHINA)					
	KISTRON	(KOREA/CHINA)					
	SUNG NAM	(KOREA/CHINA)					
SYNTHETIC RUBBER	CCW/ZHE JIANG TIAN TAI						
	ZHE JIANG TIAN HUA	(CHINA)					
	MOO DEUNG	(KOREA/CHINA)					
P.E.T(Poly Ethlylene Terephthalate Resin)	SUZHOU QILIAN						
	YUN LIN PLASTIC	(CHINA)					
	ZHANG JIA GANG LIAN YI						
	LIN AN AO XING						
ALUMINUM 99.0 % OVER	NANTONG CHUANGJIA						
	DONG NAM						
	D.N TECH/HA NAM	(KOREA/CHINA)					
	K.D.K/JCC/MATSUSHITA	(JAPAN)					
	SAM YOUNG	(KOREA)					
	BECROMAL	(ITALY)					
	-	(FRANCE)					
FORMED ALUMINUM 99.9 % OVER	HEC	· · · ·					
	XINJIANG JOINWORLD	(CHINA)					
	HUAFENG / HISTAR /RAOIO						
		(TAIWAN)					
		(KOREA)					
		(JAPAN)					
ETCHED ALUMINUM 98.0 % OVER							
		(CHINA)					
	KAN/LUNAN	(CHINA)					
INSULATION PAPER	-	(GERMANY)					
	N.K.K	(JAPAN)					
		. ,					
POLY PROPYLENE OR POLY IMIDE FILM	NITTO/NICHIBAN	(JAPAN)					
	TINNED COPPER - PLY WIRE(Pb-FREE) ALUMINUM 99.92 % OVER SYNTHETIC RUBBER	TINNED COPPER - PLY WIRE(Pb-FREE) KISTRON KISTRON KOHOKU NANTONG HONG YANG KANG WON AUTO FITTING ALUMINUM 99.92 % OVER NAN TONG HUI FENG NANTONG HONG YANG KOHOKU KOHOKU KISTRON SYNTHETIC RUBBER SUNG NAM P.E.T(Poly Ethlylene Terephthalate Resin) SUZHOU QILIAN YUN LIN PLASTIC ZHANG JIA GANG LIAN YI LIN AN AO XING NANTONG CHUANGJIA DONG NAM D.N TECH/HA NAM K.D.K/JCC/MATSUSHITA SAM YOUNG BECROMAL SATMA HEC XINJIANG JOINWORLD HUAFENG / HISTAR /RAOIO LUXON/LITON K-JCC K.D.K ETCHED ALUMINUM 98.0 % OVER K-JCC INSULATION PAPER KAN/LUNAN					

When using aluminum electrolytic capacitors, pay strict attention to the following:

1. Electrolytic capacitors for DC application require polarization.

Confirm the polarity. If used in reversed polarity, the circuit life may be shortened or the capacitor may be damaged. For use on circuits whose polarity is occasionally reversed, or whose polarity is unknown, use bi-polarized capacitors (BP-series). Also, note that the electrolytic capacitor cannot be used for AC application.

2. Do not apply a voltage exceeding the capacitor's voltage rating. If a voltage exceeding the capacitor's voltage rating is applied, the capacitor may be damaged as leakage current increases. When using the capacitor with AC voltage superimposed on DC voltage, care must be exercised that the peak value of AC voltage does not exceed the rated voltage.

3. Do not allow excessive ripple current to pass. Use the electrolytic capacitor at current values within the permissible ripple range. If the ripple current exceeds the specified value, request capacitors for high ripple current applications.

- 4. Ascertain the operating temperature range. Use the electrolytic capacitors according to the specified operating temperature range.Usage at room temperature will ensure longer life.
- 5. The electrolytic capacitor is not suitable for circuits in which charge and discharge are frequently repeated. If used in circuits in which charge and discharge are frequently repeated, the capacitance value may drop, or the capacitor may be damaged. Please consult our engineering department for assistance in these applications.
- 6. Apply voltage treatment to the electrolytic capacitor which has been allowed to stand for a long time. If the electrolytic capacitor is allowed to stand for a long time, its withstand voltage is liable to drop, resulting in increased leakage current. If the rated voltage is applied to such a product, a large leakage current occurs and this generates internal heat, which damaged the capacitor. If the electrolytic capacitor is allowed to stand for a long time, therefore, use it after giving voltage treatment (Note 1). (However, no voltage treatment is required if the electrolytic capacitor is allowed to stand for less than 2 or 3 years at normal temperature.)

7. Be careful of temperature and time when soldering.

When soldering a printed circuit board with various, components, care must be taken that the soldering temperature is not too high and that the dipping time is not too long. Otherwise, there will be adverse effects on the electrical characteristics and insulation sleeve of electrolytic capacitors in the case of small-sized electrolytic capacitors, nothing abnormal will occur if dipping is performed at less than 260 $^{\circ}$ C for less than 10 seconds.

8. Do not place a soldering iron on the body of the capacitor.

The electrolytic capacitor is covered with a vinyl sleeve. If the soldering iron comes in contact with the electrolytic capacitor body during wiring, damage to the vinyl sleeve and/or case may result in defective insulation, or improper protection of the capacitor element.

9. Cleaning circuit boards after soldering.

Some solvents have adverse effects on capacitors. Please refer to the next page.

10.Do not apply excessive force to the lead wires or terminals.

If excessive force is applied to the lead wires and terminals, they may be broken or their connections with the internal elements may be affected. (For strength of terminals, refer to KS C IEC 60384-4(JIS C5101-1, JIS C5101-4)

11.Care should be used in selecting a storage area.

If electrolytic capacitors are exposed to high temperatures caused by such things as direct sunlight, the life of the capacitor may be adversely affected. Storage in a high humidity atmosphere may affect the solderability of lead wires and terminals.

12.Surge voltage.

The surge voltage rating is the maximum DC over-voltage to which the capacitor may be subjected for short periods not exceeding approximately 30 seconds at infrequent intervals of not more than six minutes. According to KS C IEC 60384 -4, the test shall be conducted 1000 cycles at room temperature for the capacitors of characteristic KS C IEC 60384-4 or at the maximum operating temperature for the capacitors of characteristics B and C of KS C IEC 60384-4 with voltage applied through a series resistance of 1000 ohms without discharge. The electrical characteristics of the capacitor after the test are specified in KS C IEC 60384-4. Unless otherwise specified, the rated surge voltage are as follows:

Rated Voltage(V)	2	4	6.3	10	16	25	35	50	63	80	100	160	200	250	315	350	400	450	500
Rated Surge Voltage(V)	2.5	5	8	13	20	32	44	63	79	100	125	200	250	300	365	400	450	500	550

Note 1 Voltage treatment ... Voltage treatment shall be performed by increasing voltage up to the capacitor's voltage rating gradually while lowering the leakage current. In this case, the impressed voltage shall be in the range where the leakage current of the electrolytic capacitor is less than specified value. Meanwhile, the voltage treatment time may be effectively shortened if the ambient temperature is increased (within the operating temperature range).
 Note 2 For methods of testing, refer to KS C IEC 60384-4, (JIS C 5101-1, JIS C 5101-4)

CLEANING CONDITIONS

Aluminum electrolytic capacitors that have been exposed to halogenated hydrocarbon cleaning and defluxing solvents are susceptible to attack by these solvents. This exposure can result in solvent penetration into the capacitors, leading to internal corrosion and potential failure.

Common type of halogenated cleaning agents are listed below.

Chemical Name	Structural Formula	Representatice Brand Name
Trichlorotrifluoroethane	C2CI3F3	Freon TF,Daiflon S-3
Fluorotrichloromethane	CCI₃F	Freon-11,Daiflon S-1
1,1,1-Trichloroethane	F ₂ H ₃ CI ₃	Chloroethane
Trichloroethylene	C2HCI3	Trichiene
Methyl Chloride	CH₃CI	MC

We would like to recommend you the below cleaning materials for your stable cleaning condition taking the place of previous materials.

◎ Isopropyl Alcohol(IPA) or Water

Cleaning method: One of immersion, ultrasonic or vapor cleaning.

Maximum cleaning time: 5 minutes(Chip type: 2 minutes)

※Do not use AK225AES

Aluminum electrolytic capacitors are easily affeceted by halogen ions, particularly by chloride ions. Excessive amounts of halogen ions, if happened to enter the inside of the capacitors, will give corrosion accidents-rapid capacitance drop and vent open. The extent of corrosion accidents varies with kinds of electrolytes and seal-materials. Therefore, the prevention of halogen ion contamination is the most improtant check point for quality control in our procuction lines. At present, halogenated hydrocarbon-contained organic solvents such as Trichloroethylene, 1,1,1-Trichloroethane, and Freon are used to remove flux from circuit boards.

If electroytic capacitors are cleaned with such solvents, they may gradually penetrate the seal portion and cause the eosion. When using latex-based adhesive on the capacitors rubber end seal for adhesion to a PCB, corrosion may occur depending on the kind of solvent in the adhesive. Select an adhesive as an organic solvent with dissolved polymer that is not halogenated hydrocarbon. Hot air drying is required for eliminating the solvent between the product and the PCB at 50° C ~ 80° C after coating.

Followings are the penetration path of the halogenated solvent.

① Penetration between the rubber and the aluminum case

2 Penetration between the rubber and the lead wire

3 Penetration through the rubber

The inside of the capacitors, the mechanism of corrosion of aluminum electrolytic capacitors by halogen ions can be explained as follows:

Halides(RX) are absorbed and diffused into the seal portion. The halides then enter the inside of the capacitors and contact with the electrolyte of the capacitors. Where by halogen ions are made free by a hydrolysis with water in the electrolyte:

 $RX + H_2O \rightarrow ROH + H^+ + X^-$

The halogen ions (X⁻) react with the dielectric substance(Al₂O₃) of aluminum electrolytic capacitors:

 $AI_2O_3 + 6H^+ + 6X^- \rightarrow 2ALX_3 + 3H_2O$

AIX₃ is dissociated with water:

$$ALX_3 + 3H_2O \rightarrow AL (OH)_3 + 3H^+ + 3X^-$$