FUZETEC TECHNOLOGY CO., LTD.	NO. PQ34-102E			2E
Product Specification and Approval Sheet	Version	3	Page	1/3

# Radial Leaded PTC Resettable Fuse: FRK050-60F

### 1. Summary

(a) RoHS Compliant (Lead Free) product

(b) Applications: Wide variety of electronic equipment

(c) Product Features: Solid state, Radial leaded product ideal for up to 60V<sub>DC</sub>

(d) Operation Current: 0.50A

(e) Maximum Operation Voltage: 60V<sub>DC</sub> (f) Temperature Range : -40°C to 85°C

### 2. Agency Recognition

UL: **Pending** C-UL: Pending TÜV: **Pending** 

### 3. Electrical Characteristics (23°℃)

Dort	Hold	Trip	Max.Time to Trip		Max.	Rated	Тур.	Resis	tance
Part	Current	Current			Current	Voltage	Power	RMIN	R1MAX
Number	IH, A	IT, A	I, A	Time,s	IMAX, A	VMAX, VDC	Pd, W	Ohms	Ohms
FRK050-60F	0.50	1.00	8.0	0.8	40	60	1.00	0.320	0.900

I<sub>H</sub>=Hold current-maximum current at which the device will not trip at 23℃ still air. I<sub>T</sub>=Trip current-minimum current at which the device will always trip at 23°C still air.

V<sub>MAX</sub>=Maximum voltage device can withstand without damage at its rated current.

I MAX = Maximum fault current device can withstand without damage at rated voltage (V MAX). Pd=Typical power dissipated from device when in tripped state in 23°C still air environment.

R<sub>MIN</sub>=Minimum device resistance at 23°C


R<sub>1MAX</sub>=Maximum device resistance at 23°C, 1 hour after tripping.

Physical specifications:

Lead material: Tin plated copper,24AWG. Soldering characteristics:MIL-STD-202, Method 208E.

Insulating coating:Flame retardant epoxy, meets UL-94V-0 requirement.

## 4. Production Dimensions (millimeter)




FRK050-60F Lead Size: 24AWG Φ 0.51 mm Diameter

Part	Α	В	С	D E		F	
Number	Maximum	Maximum	Typical	Minimum	Maximum	Typical	
FRK050-60F	7.10	11.43	5.1	7.6	3.56	1.1	


NOTE: Specification subject to change without notice.

FUZETEC TECHNOLOGY CO., LTD.	NO.	PQ34-102E		
<b>Product Specification and Approval Sheet</b>	Version	3	Page	2/3

# 5. Thermal Derating Curve



# 



NOTE: Specification subject to change without notice.

FUZETEC TECHNOLOGY CO., LTD.	NO. PQ34-1			02E	
Product Specification and Approval Sheet	Version	3	Page	3/3	

### 7. Material Specification

Lead material: Tin plated copper, 24 AWG.

Soldering characteristics:MIL-STD-202, Method 208E.

Insulating coating:Flame retardant epoxy, meets UL-94V-0 requirement

### 8. Part Numbering and Marking System

#### **Part Numbering System** Part Marking System $FRK \square \square \square - \square \square F$ Fuzetec Logo RK50F RoHS Compliant / Lead Free RK □ F 31BD Voltage Rating RoHS Compliant / Lead Free Part Identification Current Rating **Product Family** Example - Date Code/Lot Number

Note: Font on Marking may look slightly different due to fine turnings of each Marking printer.

**Warning:** -Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



- -PPTC device are intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated.
- Avoid contact of PPTC device with chemical solvent. Prolonged contact will damage the device performance.

NOTE: Specification subject to change without notice.