





## SPECIFICATIONS

Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°c to +105°c  
 Contact Material: Brass  
 Contact Plating: Au3U Over Ni  
 Insulator Material: Polyester(UL94V-0)  
 Standard: PA6T  
 Max. Processing Temp: 230° C for 30-60 seconds  
 (260° C for 10 seconds)



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE ± 0.05)



OPERATION		DRAW		YTYuSheng		12.03.28		SCALE		FIT	
X.X		±0.30		YTYuSheng		12.03.28		UNIT		mm	
X.XX		±0.20		CHECK				SIZE		A4	
X.XXX		±0.10		APPROVE				SHEET		1/1	
Angle		±3°		PROJ.				PROJ.		◆	
DIM		TOL									
REV		DATE		MODIFICATION DESCRIPTION		CHANGE		5		7	
1		2		3		4		5		7	
A		A0		NEW DRAWING				PART NO.		PH-00347---A0001	
REV		DATE		MODIFICATION DESCRIPTION		CHANGE		TITLE:		2.54PH H2.5mm 2X19P DIP PA7.7 PC3.0	
1		2		3		4		5		7	

深圳市连盛精密连接器有限公司

PH-00347---A0001

2.54PH H2.5mm 2X19P DIP PA7.7 PC3.0