





# RoHS

## SPECIFICATIONS

Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C  
 Contact Material: Brass  
 Contact Plating: Au Over Ni  
 Insulator Material: Polyester(UL94V-0)  
 Standard: PA6T  
 Max. Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Recommended P.C.B Layout (Top Side)  
 (PCB BOARD TOLERANCE ±0.05)



Dimension antitheses list				
ITEM	PA	PC	L	
Standard	7.00	3.00	12.50	
Alternate				

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30			UNIT	mm			PH-00602	PH-00602
X.XX	±0.20	CHECK		SIZE	A4			---	A0001
X.XXX	±0.10			SHEET	1/1				
Angle	±3°	APPROVE		PROJ.					
DIM	TOL								
REV		DATE		MODIFICATION DESCRIPTION		CHANGE		TITLE:	
1		2012.03.28		NEW DRAWING				2.54PH H2.5mm 2x20P 180°	