





RoHS

SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C
 Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



料号: PH-00650

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	6.00	4.44	7.80	12.4
Alternate				

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	X.XX	±0.20	UNIT	mm	SIZE	A4
A1	2017.12.19	NEW DRAWING		CHECK		SHEET	1/1
A0	2012.04.11	NEW DRAWING		APPROVE		PROJ.	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	PART NO. PH-00650---A0001	
1						TITLE: 2.54PH H=2.5 2x20pin SMT=7.8 PA6.0 PB4.44 L=12.4 AU0.8U PA6T 带偏柱 直径1.5 高2.9 间距之间 38.46	