


REVISION	DESCRIPTION	DATE	DRAFTER
A0	首次发行	21.01.16	S. He



裁线图
 P1 90度 SMA母头母针 微细同轴电缆, OD1.13mm, 双锡黑色 P2 MHF-1 PLUG

技术要求:

- 1 装配要求: 母针不可有凸出及下陷现象, 详细接受范围由工程人员或品质人员判定;
- 2 方向要求: MHF-1 PLUG开口面与SMA剖面朝向如图所示, 公差±45°;
- 3 电气特性: 特性阻抗:50Ω; 适用频率范围:DC-6GHz;
- 4 断短路与高压测试: 100%使用线材综合测试仪测试。
 测试条件: 断短路判定值:2kΩ;直流通电电阻:最大2.00Ω;绝缘电阻:DC 300V, 0.05秒, 50MΩ。
- 5 拔出力测试: 最小1.30kgf。
 测试方法: 沿电缆中心轴, 以约25±3毫米/分钟的速度, 垂直将1.30kg砝码提高桌面即为合格。
- 6 尺寸检验: [*]为FAI检测项目; *为重点检测项目; ■为CPK管制项目。
- 7 外观检验: 目视全检。产品表面不得有刮伤、破损和脏污; 镀层色泽光亮均匀, 不得有氧化。
- 8 包装规范: 25PCS/扎, 2扎/包, 即50PCS/包。
- 9 环保要求: 产品及其使用之物料皆需要符合RoHS要求。

No.	PART NUMBER	PART NAME & DESCRIPTION	Q' TY	REMARKS
7	2TA035BK1-010	热缩套管, 单壁普通型, ∅3.5*1.0, 黑色	1	---
6	2LC15SF103-7	SMA 助推管镀金 FOR 1.13线	1	---
5	2LC15SF103-6	TPFE 绝缘粒, OD:2.4*T0.7	1	---
4	2LC15SF103-5	SMA 母针, 镀金	1	---
3	2LC15SF103-1	90度SMA母头镀金, SQ7.0*L16.8*W13.6mm	1	---
2	2LM10P113210	MHF I PLUG FOR OD1.13 CABLE	1	---
1	2C5M11312BK1	OD1.13黑色双锡线-50 OHM	1	---

GENERAL TOLERANCE: LINEAR: X ±3.00 X.X ±1.00 X.XX ±0.50 X.XXX ±0.05 ANGLE: X° ±45.00° X.X° ±15.00° X.XX° ±2.00° X.XXX° ±1.00°		HJ-Tech 东莞市皇捷通讯科技有限公司 手机: 15015262131/13714786106	
FILE NAME: 产品图	TITLE: 射频电缆组件 1.13双锡线黑色, P1端90度SMA母头母针, P2端打一代端子, 外露线长135mm	P/N: HJ-1.13-SMA-IPEX1-135mm	
ENG/DATE: XIU HE/20.08.11	SCALE: 1:1	REVISION: A0	SHEET: 1/1
CHE/DATE:	UNIT: mm		
APP/DATE:			

COMPLIANCE WITH THE REQUIREMENT: ■RoHS; □HF; □SONY SS-00259; □OTHERS H514
 *NO USING ESTRICTED AND BANNED SUBSTANCE