



## HD60N08 / HU60N08

### 80V N-Channel MOSFET

|                           |
|---------------------------|
| $BV_{DSS} = 80V$          |
| $R_{DS(on)} = 13 m\Omega$ |
| $I_D = 60 A$              |



### FEATURES

- Originative New Design
- Superior Avalanche Rugged Technology
- Robust Gate Oxide Technology
- Very Low Intrinsic Capacitances
- Excellent Switching Characteristics
- Unrivalled Gate Charge : 40 nC (Typ.)
- Extended Safe Operating Area
- Lower  $R_{DS(ON)}$  : 0.013  $\Omega$  (Typ.) @  $V_{GS}=10V$
- 100% Avalanche Tested

### Absolute Maximum Ratings $T_C=25^\circ C$ unless otherwise specified

| Symbol         | Parameter   | Value       | Units         |
|----------------|---|-------------|---------------|
| $V_{DSS}$      | Drain-Source Voltage  | 80          | V             |
| $I_D$          | Drain Current – Continuous ( $T_C = 25^\circ C$ )                             | 60          | A             |
|                | Drain Current – Continuous ( $T_C = 100^\circ C$ )                            | 41          | A             |
| $I_{DM}$       | Drain Current – Pulsed (Note 1)   | 100         | A             |
| $V_{GS}$       | Gate-Source Voltage   | $\pm 20$    | V             |
| $E_{AS}$       | Single Pulsed Avalanche Energy (Note 2)                                       | 290         | mJ            |
| $I_{AR}$       | Avalanche Current (Note 1)  | 60          | A             |
| $E_{AR}$       | Repetitive Avalanche Energy (Note 1)  | 12          | mJ            |
| dv/dt          | Peak Diode Recovery dv/dt (Note 3)  | 7.0         | V/ns          |
| $P_D$          | Power Dissipation ( $T_A = 25^\circ C$ )*                                     | 3.75        | W             |
|                | Power Dissipation ( $T_C = 25^\circ C$ )                                      | 85          | W             |
|                | - Derate above $25^\circ C$   | 0.8         | W/ $^\circ C$ |
| $T_J, T_{STG}$ | Operating and Storage Temperature Range                                       | -55 to +150 | $^\circ C$    |
| $T_L$          | Maximum lead temperature for soldering purposes, 1/8" from case for 5 seconds | 300         | $^\circ C$    |

### Thermal Resistance Characteristics

| Symbol          | Parameter            | Typ. | Max. | Units        |
|-----------------|----------------------|------|------|--------------|
| $R_{\theta JC}$ | Junction-to-Case     | --   | 1.0  | $^\circ C/W$ |
| $R_{\theta JA}$ | Junction-to-Ambient* | --   | 40   |              |
| $R_{\theta JA}$ | Junction-to-Ambient  | --   | 62.5 |              |

\* When mounted on the minimum pad size recommended (PCB Mount)

80V<sub>DS</sub> / ±25V<sub>GS</sub> / 80A(I<sub>D</sub>) N-Channel Enhancement Mode MOSFET

## N-Channel Enhancement Mode MOSFET2

### Electrical Characteristics (T<sub>C</sub>=25°C unless otherwise noted)


| Parameter                                 | Symbol              | Condition  | Min | Typ  | Max  | Unit |
|---|---------------------|--|-----|------|------|------|
| <b>Off Characteristics</b>                |                     |  |     |      |      |      |
| Drain-Source Breakdown Voltage            | BV <sub>DSS</sub>   | V <sub>GS</sub> =0V I <sub>D</sub> =250μA  | 80  | -    | -    | V    |
| Zero Gate Voltage Drain Current           | I <sub>DSS</sub>    | V <sub>DS</sub> =80V, V <sub>GS</sub> =0V  | -   | -    | 1    | μA   |
| Gate-Body Leakage Current                 | I <sub>GSS</sub>    | V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V   | -   | -    | ±100 | nA   |
| <b>On Characteristics (Note 3)</b>        |                     |  |     |      |      |      |
| Gate Threshold Voltage                    | V <sub>GS(th)</sub> | V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA   | 2   | 3    | 4    | V    |
| Drain-Source On-State Resistance          | R <sub>DS(ON)</sub> | V <sub>GS</sub> =10V, I <sub>D</sub> =40A  | -   | 13   | 16   | mΩ   |
| Forward Transconductance                  | g <sub>FS</sub>     | V <sub>DS</sub> =5V, I <sub>D</sub> =40A   | 30  | -    | -    | S    |
| <b>Dynamic Characteristics (Note4)</b>    |                     |  |     |      |      |      |
| Input Capacitance                         | C <sub>iss</sub>    | V <sub>DS</sub> =25V, V <sub>GS</sub> =0V,<br>F=1.0MHz   | -   | 2498 | -    | PF   |
| Output Capacitance                        | C <sub>oss</sub>    |  | -   | 185  | -    | PF   |
| Reverse Transfer Capacitance              | C <sub>rss</sub>    |  | -   | 80   | -    | PF   |
| <b>Switching Characteristics (Note 4)</b> |                     |  |     |      |      |      |
| Turn-on Delay Time                        | t <sub>d(on)</sub>  | V <sub>DD</sub> =30V, I <sub>D</sub> =2A, R <sub>L</sub> =1Ω<br>V <sub>GS</sub> =10V, R <sub>GEN</sub> =3Ω | -   | 12   | -    | nS   |
| Turn-on Rise Time                         | t <sub>r</sub>      |  | -   | 5.2  | -    | nS   |
| Turn-Off Delay Time                       | t <sub>d(off)</sub> |  | -   | 38   | -    | nS   |
| Turn-Off Fall Time                        | t <sub>f</sub>      |  | -   | 27   | -    | nS   |
| Total Gate Charge                         | Q <sub>g</sub>      | V <sub>DS</sub> =30V, I <sub>D</sub> =40A,<br>V <sub>GS</sub> =10V   | -   | 36   | -    | nC   |
| Gate-Source Charge                        | Q <sub>gs</sub>     |  | -   | 9.9  | -    | nC   |
| Gate-Drain Charge                         | Q <sub>gd</sub>     |  | -   | 6.6  | -    | nC   |
| <b>Drain-Source Diode Characteristics</b> |                     |  |     |      |      |      |
| Diode Forward Voltage (Note 3)            | V <sub>SD</sub>     | V <sub>GS</sub> =0V, I <sub>S</sub> =40A   | -   | -    | 1.2  | V    |
| Diode Forward Current (Note 2)            | I <sub>S</sub>      |  | -   | -    | 90   | A    |
| Reverse Recovery Time                     | t <sub>rr</sub>     | T <sub>J</sub> = 25°C, I <sub>F</sub> =40A<br>di/dt = 100A/μs (Note3)                                      | -   | 35   |      | nS   |
| Reverse Recovery Charge                   | Q <sub>rr</sub>     |  | -   | 47   |      | nC   |
| Forward Turn-On Time                      | t <sub>on</sub>     | Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)                                       |     |      |      |      |

### Notes:


1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. Surface Mounted on FR4 Board, t ≤ 10 sec.
3. Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.
4. Guaranteed by design, not subject to production
5. E<sub>AS</sub> condition: T<sub>J</sub>=25°C, V<sub>DD</sub>=30V, V<sub>G</sub>=10V, L=0.5mH, R<sub>g</sub>=25Ω

**Test circuit**


**1) E<sub>AS</sub> test Circuits**




**2) Gate charge test Circuit**




**3) Switch Time Test Circuit**




**Typical Electrical and Thermal Characteristics (Curves)**




**Figure 1 Output Characteristics**




**Figure 2 Transfer Characteristics**




**Figure 3 Rdson- Drain Current**




**Figure 4 Rdson-Junction Temperature**




**Figure 5 Gate Charge**




**Figure 6 Source- Drain Diode Forward**




**Figure 7 Capacitance vs Vds**




**Figure 9 Power De-rating**



**Figure 8 Safe Operation Area**




**Figure 10 ID Current- Junction Temperature**



**Figure 11 Normalized Maximum Transient Thermal Impedance**

Package Dimension


TO-252



HD60N80\_HU60N80

Package Dimension

TO-251



HD60N80\_HU60N80  
7