





RoHS

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Phosphor Bronze
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



| | | | | | | | | | | | | |
|-----|------|--------------------------|--------|-----------|-------|---------|--|-------|-----|----------------|--|------------------------------|
| | | | | OPERATION | | DRAW | | SCALE | FIT | 深圳市连盛精密连接器有限公司 | | |
| | | | | X.X | ±0.30 | | | UNIT | mm | | | |
| | | | | X.XX | ±0.20 | CHECK | | SIZE | A4 | PART NO. | | FH-00506 |
| | | | | X.XXX | ±0.10 | | | SHEET | 1/1 | TITLE: | | 2.0FH H2.20mm 2x13pin SMT 带柱 |
| REV | DATE | MODIFICATION DESCRIPTION | CHANGE | DIM | TOL | APPROVE | | PROJ. | | | | |
| 1 | 2 | 3 | 4 | 5 | 6 | | | 7 | 8 | 9 | | |