



Poles	DIM.A	DIM.B	DIM.C
2P	4.25	1.25	7.3
3P	5.50	2.50	8.5
4P	6.75	3.75	9.8
5P	8.00	5.00	11.0
6P	9.25	6.25	12.3
7P	10.50	7.50	13.5
8P	11.75	8.75	14.8
9P	13.00	10.00	16.0
10P	14.25	11.25	17.3
11P	15.50	12.50	18.5
12P	16.75	13.75	19.8
13P	18.00	15.00	21.0
14P	19.25	16.25	22.3
15P	20.50	17.50	23.5
16P	21.75	18.75	24.8



■ 技术参数 SPECIFICATIONS

- ◆ 适用线规: AWG.#28~#32
 - ◆ Applicable Wire: AWG.#28~#32
 - ◆ 额定电压: 125V DC/AC(rms)
 - ◆ Rated voltage: 125V DC/AC(rms)
 - ◆ 额定电流: 1A (AWG.#28)
 - ◆ Rated Current: 1A (AWG.#28)
 - ◆ 耐压值: 250V AC/minute
 - ◆ Withstand voltage: 250V AC/min.
 - ◆ 工作温度: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 - ◆ Working Temp : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 - ◆ 绝缘电阻: $\geq 100 \text{ M}\Omega$
 - ◆ Insulation resistance: $\geq 100 \text{ M}\Omega$
 - ◆ 接触电阻: $\leq 20 \text{ m}\Omega$
 - ◆ Contact resistance: $\leq 20 \text{ m}\Omega$
- 材料 MATERIAL
- ◆ 绝缘体: 尼龙9T, UL94-V0
 - ◆ Insulator: PA9T, UL94-V0
 - ◆ 接触针: 磷铜
 - ◆ Contact PIN: Phosphor bronze
 - ◆ 焊片: 磷铜
 - ◆ Solder tab: Phosphor bronze

APPROVALS		DATE	
DRAWN	ZHIWEI,CHEN	2017.09.13	
CHECKED			
APPROVALS			
TOLERANCES ARE		30~0.15	±0.30
		10~30	±0.20
		5~10	±0.15
		~ 5	±0.10
ANGLE		±2°	
PART NO.	TITLE: 1. 25mm SMT 立式		
UNIT: mm	GP01-1250WVS-NP		
SCALE: 1:1	PROJ:		
DRAWING NO.	SHEET 1 OF 1		
ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW