

MT3520B

2A,2.3V-6V Input,1.5MHz Synchronous Step-Down Converter

FEATURES


- High Efficiency: Up to 96%
- **1.5MHz Constant Frequency Operation**
- 2A Output Current
- No Schottky Diode Required
- 2.3V to 6V Input Voltage Range
- Output Voltage as Low as 0.6V
- PFM Mode for High Efficiency in Light Load
- 100% Duty Cycle in Dropout Operation
- Low Quiescent Current: 40μ A
- Short Circuit Protection
- **Thermal Fault Protection**
- Inrush Current Limit and Soft Start
- $<1\mu$ A Shutdown Current
- SOT23-5 package

APPLICATIONS

- **Cellular and Smart Phones**
- Wireless and DSL Modems
- PDAs
- Portable Instruments
- **Digital Still and Video Cameras**
- PC Cards

GENERAL DESCRIPTION

The MT3520B is a 1.5MHz constant frequency. current mode step-down converter. It is ideal for portable equipment requiring very high current up to 2A from single-cell Lithium-ion batteries while still achieving over 90% efficiency during peak load conditions. The MT3520B also can run at 100% duty cycle for low dropout operation, extending battery life in portable systems while light load operation provides very low output ripple for noise sensitive applications. The MT3520B can supply up to 2A output load current from a 2.3V to 6V input voltage and the output voltage can be regulated as low as 0.6V. The high switching frequency minimizes the size of external components while keeping switching losses low. The internal slope compensation setting allows the device to operate with smaller inductor values to optimize size and provide efficient operation. The MT3520B is offered in a low profile 6-pin, SOT package, and is available in an adjustable version. This device offers two operation modes, PWM control and PFM Mode switching control, which allows a high efficiency over the wider range of the load.





www.aerosemi.com Aerosemi Proprietary Information.Unauthorized Photocopy and Duplication Prohibited. All Rights Reserved.

95.009

ABSOLUTE MAXIMUM RATINGS (Note 1)

Input Supply Voltage	0.3V to 6.5V
EN,FB Voltages	0.3V to (V _{IN} +0.3V)
SW Voltage	0.3V to (V _{IN} +0.3V)
Power Dissipation	0.6W
Thermal Resistance θ_{JC}	130°C/W
Thermal Resistance θ_{JA}	250°C/W

Junction Temperature(Note2).....150°C Operating Temperature Range......-40°C to 85°C Storage Temperature Range......-65°C to 150°C ESD HBM(Human Body Mode).....2kV ESD MM(Machine Mode)......200V

PACKAGE/ORDER INFORMATION

TOP VIEW	Order Part Number	Package	Top Marking
GND 2 SW 3 4 VIN	MT3520B	SOT23-5	AS20B5
5-LEAD PLASTIC SOT-23 $T_{JMAX} = 150^{\circ}C, \theta_{JA} = 250^{\circ}C/ \text{ W}, \theta_{JC} = 130^{\circ}C/W$			

Pin Number Description Pin Name Chip Enable Pin. Drive EN above 1.5V to turn on the part. Drive EN below 1 ΕN 0.3V to turn it off. Do not leave EN floating. GND 2 Analog ground pin. Power Switch Output. It is the switch node connection to Inductor. This SW pin connects to the drains of the internal P-ch and N-ch MOSFET 3 switches. VIN 4 Analog supply input pin. Output Voltage Feedback Pin. An internal resistive divider divides the FB 5 output voltage down for comparison to the internal reference voltage.

PIN DESCRIPTION

ELECTRICAL CHARACTERISTICS (Note 3)


$(V_{IN} = V_{EN} = 3.6V, V_{OUT} = 1.8V)$	Y , $I_A = 25$ °C, unless otherwise noted.)				
PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
Input Voltage Range		2.3		6	V
UVLO Threshold		1.7	1.9	2.1	V
Input DC Supply Current	(Note 4)				μA
PWM Mode	$V_{OUT} = 90\%, I_{LOAD} = 0mA$		150	300	μA
PFM Mode	$V_{out} = 105\%, I_{LOAD} = 0mA$		40	75	μA
Shutdown Mode	$V_{EN} = 0V, V_{IN} = 4.2V$		0.1	1.0	μA
Regulated Feedback	$T_A = 25^{\circ}C$	0.588	0.600	0.612	V
Voltage V_{FB}	$T_A = 0^{\circ}C \leqslant T_A \leqslant 85^{\circ}C$	0.586	0.600	0.613	V
Voltage V _{FB}	$T_A = -40^{\circ}C \leq T_A \leq 85^{\circ}C$	0.585	0.600	0.615	V
Reference Voltage Line Regulation	V_{IN} =2.5V to 5.5V		0.1		%/V
Output Voltage Accuracy	$V_{IN} = 2.5V$ to 5.5V, $I_{OUT} = 10$ mA to 2000mA	-3		+3	% V_{out}
Output Voltage Load Regulation	I _{out} =10mA to 2000mA		0.2		%/A
Oscillation Frequency	V _{OUT} =100%		1.5		MHz
Oscillation requelley	$V_{OUT} = 0V$		300		kHz
On Resistance of PMOS	I _{sw} =100mA	×	100	150	mΩ
On Resistance of NMOS	I _{sw} =-100mA		80	150	mΩ
Peak Current Limit	$V_{IN} = 3V, V_{OUT} = 90\%$		4		А
EN Threshold		0.30	1.0	1.50	V
EN Leakage Current			±0.01	±1.0	μA
SW Leakage Current	$V_{EN} = 0V, V_{IN} = V_{SW} = 5V$		±0.01	±1.0	μA


Note 1: Absolute Maximum Ratings are those values beyond which the life of a device may be impaired. **Note 2:** T_J is calculated from the ambient temperature T_A and power dissipation P_D according to the following formula: $T_J = T_A + (P_D) \times (250^{\circ}C/W)$.

Note 3: 100% production test at $+25^{\circ}$ C. Specifications over the temperature range are guaranteed by design and characterization.


Note 4: Dynamic supply current is higher due to the gate charge being delivered at the switching frequency.


TYPICAL PERFORMANCE CHARACTERISTICS







Vin=3.6V,Vout=1.8V












MT3520B Rev1.0



MT3520B Rev1.0

FUNCTIONAL BLOCK DIAGRAM




Figure 2. MT3520B Block Diagram

MT3520B Rev1.0

FUNCTIONAL DESCRIPTION

The MT3520B is a high output current monolithic switch mode step-down DC-DC converter. The device operates at a fixed 1.5MHz switching frequency, and uses a slope compensated current mode architecture. This step-down DC-DC converter can supply up to 2A output current at $V_{IN} = 3.6V$ and has an input voltage range from 2.3V to 6V. It minimizes external component size and optimizes efficiency at the heavy load range. The slope compensation allows the device to remain stable over a wider range of inductor values so that smaller values $(1\mu H \text{ to } 4.7\mu H)$ with lower DCR can be used to achieve higher efficiency. Only a small bypass input capacitor is required at the output. The adjustable output voltage can be programmed with external feedback to any voltage, ranging from 0.6V to near the input voltage. It uses internal MOSFETs to achieve high efficiency and can generate very low output voltages by using an internal reference of 0.6V. At dropout operation, the converter duty cycle increases to 100% and the output voltage tracks the input voltage minus the low R_{DS(ON)} drop of the P-channel high-side MOSFET and the inductor internal amplifier DCR. The error and compensation provides excellent transient response, load and line regulation. Internal soft start eliminates any output voltage overshoot when the enable or the input voltage is applied.

Setting the Output Voltage

Figure 1 shows the basic application circuit for the MT3520B. The MT3520B can be externally programmed. Resistors R1 and R2 in Figure 1 program the output to regulate at a voltage higher than 0.6V. To limit the bias current required for the external feedback resistor string while maintaining good noise immunity, the minimum suggested value for R2 is $59k\Omega$. Although a larger value will further reduce quiescent current, it will also increase the impedance of the feedback node, making it more sensitive to external noise and interference. Table 1 summarizes the resistor values for various output voltages with R2 set to either $59k\Omega$ for good noise immunity or $316k\Omega$ for reduced no load input current.

The external resistor sets the output voltage according to the following equation:

$$V_{0UT} = 0.6 \times \left(1 + \frac{R1}{R2}\right)$$
$$R1 = \left(\frac{V_{0UT}}{0.6} - 1\right) \times R2$$

Table 1 shows the resistor selection for different output voltage settings.

V	v	
	R2=59kΩ	R2=316kΩ
V _{OUT} (V)	R1(kΩ)	R1(kΩ)
0.8	19.6	105
0.9	29.4	158
1.0	39.2	210
1.1	49.9	261
1.2	59.0	316
1.3	68.1	365
1.4	78.7	422
1.5	88.7	475
1.8	118	634
1.85	124	655
2.0	137	732
2.5	187	1000
3.3	267	1430

Table 1: Resistor selections for different output voltagesettings (standard 1% resistors substituted forcalculated values).

APPLICATIONS INFORMATION

Inductor Selection

For most designs, the MT3520B operates with inductors of 1μ H to 4.7μ H. Low inductance values are physically smaller but require faster switching, which results in some efficiency loss. The inductor value can be derived from the following equation:

$$L = \frac{V_{\text{out}} \times (V_{\text{IN}} - V_{\text{out}})}{V_{\text{IN}} \times \Delta I_{\text{L}} \times f_{\text{0 s c}}}$$

Where Δ I_L is inductor Ripple Current. Large value inductors result in lower ripple current and small value inductors result in high ripple current. For optimum voltage-positioning load transients, choose an inductor with DC series resistance in the 50m Ω to 150m Ω range.

	PART NUMBER	VALUE (uH)	DCR (Q MAX)	MAX DC CURRENT (A)	SIZE L*W*H(mm³)	
	Sumida CDRH5D16	2.2	28.7	3	5.8x5.8x1.8	
		3.3	35.6	2.6	5.075.071.0	
		4.7	19	3.4	8.3x8.3x3.0	
		2.2	23	3.3		
Sumida CDRH5D16	3.3	29	2.6	5.2x5.2x3.0		
	001110010	4.7	39	2.1		

Table2.Recommend Surface Mount Inductors

Input Capacitor Selection

The input capacitor reduces the surge current drawn from the input and switching noise from the device. The input capacitor impedance at the switching frequency should be less than input source impedance to prevent high frequency switching current passing to the input. A low ESR input capacitor sized for maximum RMS current must be used. Ceramic capacitors with X5R or X7R dielectrics are highly recommended because of their low ESR and small temperature coefficients. A 22μ F ceramic capacitor for most applications is sufficient. A large value may be used for improved input voltage filtering.

Output Capacitor Selection

The output capacitor is required to keep the output voltage ripple small and to ensure regulation loop stability. The output capacitor must have low impedance at the switching frequency. Ceramic capacitors with X5R or X7R dielectrics are recommended due to their low ESR and high ripple current ratings. The output ripple ΔV_{OUT} is determined by:

$$\Delta V_{\text{OUT}} \leq \frac{V_{\text{OUT}} \times (V_{\text{IN}} - V_{\text{OUT}})}{V_{\text{IN}} \times f_{\text{OSC}} \times L} \times \left(\text{ESR} + \frac{1}{8 \times f_{\text{OSC}} \times C_{\text{OUT}}} \right)$$

A 22μ F ceramic can satisfy most applications.

PCB Layout Recommendations

When laying out the printed circuit board, the following checking should be used to ensure proper operation of the MT3520B. Check the following in your layout:

- The power traces, consisting of the GND trace, the SW trace and the VIN trace should be kept short, direct and wide
- ➢ Does the (+) plates of C_{IN} connect to VIN as closely as possible. This capacitor provides the AC current to the internal power MOSFETs.
- > Keep the switching node, SW, away from the sensitive V_{OUT} node.
- > Keep the (-) plates of C_{IN} and C_{OUT} as close as possible.






Figure 3. MT3520B Suggested Layout



PACKAGE DESCRIPTION






SOT23-5

5LD SOT-23 PACKAGE OUTLINE DIMENSIONS

Dimension	Min. Max.		
A	1.05	1.35	
A1	0.04	0.15	
В	0.3	0.5	
C	0.09	0.2	
D	2.8	3.0	
Н	2.5	3.1	
E	1.5	1.7	
e	0.95 REF.		
e1	1.90 REF.		
L1	0.2	0.55	
L	0.35	0.8	
Q	0°	10°	



SIDE VIEW

FRONT VIEW

NOTE:

NOTE: 1.DIMENSIONS ARE IN MILLIMETERS 2.DRAWING NOT TO SCALE 3.DIMENSIONS ARE INCLUSIVE OF PLATING 4.DIMENSIONS ARE EXCLUSIVE OF MOLD FLASH AND METAL BURR



IMPORTANT NOTICE

Xi'an Aerosemi Technology Co.,Ltd reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services.

Xi'an Aerosemi Technology Co.,Ltd is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Xi'an Aerosemi Technology Co.,Ltd does not assume any responsibility for use of any its products for any particular purpose, nor does Xi'an Aerosemi Technology Co.,Ltd assume any liability arising out of the application or use of any its products or circuits.