

INTERFACE AND SWITCHING APPLICATION.

FEATURES

- ESD Protected 2000V.
- High density cell design for low $R_{DS(ON)}$.
- Voltage controlled small signal switch.
- Rugged and reliable.
- High saturation current capability.
- Suffix U : Qualified to AEC-Q101.
ex) 2N7002KA-RTK/HU.


MAXIMUM RATING (Ta=25°C)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Drain-Source Voltage	V_{DSS}	60	V
Gate-Source Voltage	V_{GSS}	± 20	V
Drain Current	Continuous	I_D	mA
	Pulsed (Note 1)	I_{DP}	
Drain Power Dissipation (Note 2)	P_D	350	mW
Junction Temperature	T_j	150	°C
Storage Temperature Range	T_{stg}	-55 ~ 150	°C
Thermal Characteristics			
Thermal Resistance, Junction-to-Ambien (Note2)	$R_{th(j-a)}$	357	°C/W

Note 1) Pulse Width $\leq 10\mu s$, Duty Cycle $\leq 1\%$

Note 2) Package mounted on 99% Alumina $10 \times 8 \times 0.6\text{mm}$


EQUIVALENT CIRCUIT




ELECTRICAL CHARACTERISTICS (Ta=25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=10\mu A$	60	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=60V, V_{GS}=0V$	-	-	1	μA
Gate-Body Leakage, Forward	I_{GSSF}	$V_{GS}=20V, V_{DS}=0V$	-	-	10	μA
Gate-Body Leakage, Reverse	I_{GSSR}	$V_{GS}=-20V, V_{DS}=0V$	-	-	-10	μA
ESD-Capability*	-	$C=100\text{pF}, R=1.5\text{K}\Omega$ Both forward and reverse direction 3 pulse	2000	-	-	V

*Failure criterion : $I_{DSS} > 1\mu A$ at $V_{DS}=60V, I_{GSSF} > 10\mu A$ at $V_{GS}=20V, I_{GSSR} > -10\mu A$ at $V_{GS}=-20V$.



Marking



2N7002KA

ELECTRICAL CHARACTERISTICS (Ta=25°C) ON CHARACTERISTICS (Note 3)


CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Gate Threshold Voltage	V_{th}	$V_{DS}=V_{GS}, I_D=250 \mu A$	1.1	-	2.35	V
Drain-Source ON Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=500mA$	-	-	2.3	Ω
		$V_{GS}=5V, I_D=50mA$	-	1.7	2.7	
Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_S=200mA$ (Note 1)	-	-	1.15	V

Note 3) Pulse Test : Pulse Width $\leq 80 \mu s$, Duty Cycle $\leq 1\%$

DYNAMIC CHARACTERISTICS

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT	
Input Capacitance	C_{iss}	$V_{DS}=25V, V_{GS}=0V, f=1MHz$	-	18.0	-	pF	
Reverse Transfer Capacitance	C_{rss}		-	3.0	-		
Output Capacitance	C_{oss}		-	7.0	-		
Gate Resistance	R_g		-	850	-		Ω
Switching Time	Turn-On Time	t_{on}	$V_{DD}=30V, R_L=155 \Omega, I_D=190mA,$ $V_{GS}=10V$	-	15	-	nS
	Turn-Off Time	t_{off}		-	40	-	

SWITCHING TIME TEST CIRCUIT



2N7002KA

