RF Transformer

TC4-25+

50Ω

500 to 2500 MHz

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25 W
DC Current	30 mA
Darmanant damaga may assur if any of	those limits are avecaded

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2

Features

- wideband, 500-2500 MHz
- balanced transmission line with secondary center tap
- good return loss
- plastic base with leads
- aqueous washable

Applications

• PCS • cellular

CASE STYLE: AT224-1

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Pin Connections

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	3
SECONDARY	1
SECONDARY CT	2

Outline Drawing AT224-1



PCB Land Pattern




Suggested Layout, Tolerance to be within ±.002

Outline Dimensions (inch)

F	E	D	С	В	Α
.025	.040	.050	.160	.150	.150
0.64	1.02	1.27	4.06	3.81	3.81
wt	L	K	J	Н	G
grams		.030	.190	.065	.028
0.15	0.18	0.76	4.83	1.65	0.71

Config. H




Transformer Electrical Specifications


Ω RATIO (Secondary/Primary)	FREQUENCY (MHz)	INSERTION LOSS*					
		3 dB MHz	2 dB MHz	1 dB MHz			
4	500-2500	500-2500	700-1500	750-1200			

^{*} Insertion Loss is referenced to mid-band loss, 0.2 dB typ.

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
400.00	1.66	6.09	
500.00	1.07	8.37	
600.00	0.74	10.92	
700.00	0.54	13.81	
800.00	0.42	17.29	
900.00	0.38	21.02	
1000.00	0.37	22.67	
1100.00	0.40	20.79	
1200.00	0.43	18.40	
1300.00	0.48	16.41	
1400.00	0.53	14.94	
1500.00	0.59	13.79	
1600.00	0.64	12.90	
1800.00	0.74	11.65	
2000.00	0.84	10.75	
2200.00	0.96	10.03	
2400.00	1.08	9.35	
2500.00	1.14	8.96	
2800.00	1.38	7.82	
3000.00	1.59	7.06	





Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mini-Circuits: