

FEATURES

- Wide operating Voltages(V1mA):form 18V to 680V.
- Fast response to transient over-voltage and limited current.
- Low Clamping ratio and no follow-on current.
- Capable of absorbing high transient energies.

APPLICATIONS

- Transistor, Diode, IC, Thyristor or Triac semiconductor protection.
- Consumer electronics.
- Industrial electronics.
- Electronic home appliances, gas and petroleum appliances.
- Relay and electromagnetic valve surge absorption.

GENERAL CHARACTERISTICS DEFINITION

- Operating Temperature: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- Storage Temperature: $-40^{\circ}\text{C}\sim+125^{\circ}\text{C}$.
- Working Surface Temperature: $+115^{\circ}\text{C}$.
- Insulation Resistance: $>100\text{M}\Omega$.

ORDERING INFORMATION

05 D 180 L

① ② ③ ④

- ①Size: 05: $\phi 5.0\text{mm}$;
- ②Type: D: Disk, S: Square;
- ③Varistor voltage: 180: $180\times 10^0=18\text{V}$;
- ④ Tolerance, $K=\pm 10\%$, or customer special requirement;

PACKAGING


Model	Component Package	Quantity
05D180L	5.0mm	1000

ELECTRICAL CHARACTERISTIC

Part Number Φ5.0mm	Maximum allowable voltage		Varistor voltage V1.0mA (V)	Clamping voltage (Max.)		Maximum peak current (8/20μs)		Maximum Energy current (10/1000μs)		Rated power (W)	Typical capacitance (Reference) @1KHz(pf)
	AC(V)	DC (V)		VC (V)	IP (A)	Stand ard (A)	High surge (A)	Stand ard (J)	High surge (J)		
05D180L	10	14	18(15-21)	38	1	100	250	0.4	0.6	0.01	1400

DIMENSION

(unit: mm)



Part No.	D Max.	H Max.	L Min.	F±0.8	d±0.05	T Max.
05D180L	7.0	10	20	5	0.6	3.8

WAVE-SOLDERING

