

January 2016

Multilayer Low Pass Filter (2in1)

For 824-915MHz / 1710-1910MHz

DEA161910LT-9031A1

1.6x0.8mm [EIA 0603]*

* Dimensions Code JIS[EIA]



The products in this catalog will be or have been stopped production

Discontinue Issue Date	Jun. 4, 2020		
Last Purchase Order Date	Dec. 31, 2021		
Last Shipment Date	Mar. 31, 2022		

Please refer to our Web site about replacement information.

Multilayer Low Pass Filter (2in1) For 824-915MHz / 1710-1910MHz


Conformity to RoHS Directive


公TDK

DEA161910LT-9031A1


SHAPES AND DIMENSIONS

[Top view]





[Bottom view]



 Terminal functions

 1
 High Band Input port

 2
 GND

 3
 Low Band Input port


 4
 Low Band Output port

 5
 GND


 6
 High Band Output port

Dimensions in mm

RECOMMENDED LAND PATTERN



EVALUATION BOARD



Line width to be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

OROHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/

• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

DEA161910LT-9031A1

ELECTRICAL CHARACTERISTICS

LOW-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	824 to 915	—	0.47	0.60
	824 to 915		_	0.80 (–40 to +85°C)
Return Loss (dB)	824 to 915	10.03	29.2	—
Attenuation (dB)	1648 to 1830	30	40.8	—
	2472 to 2745	25	34.8	—
	3296 to 3660	20	28.3	—
	4120 to 4575	13	19.5	—
	4944 to 6405	7	15.0	—
	6500 to 12750	3	6.7	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

□HIGH-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	1710 to 1910	_	0.43	0.60
	1710 to 1910	_		0.80 (-40 to +85°C)
Return Loss (dB)	1710 to 1910	10.03	17.0	—
Attenuation (dB)	3420 to 3820	30	40.3	-
	5130 to 5730	20	26.1	_
	6840 to 9550	7	12.0	_
	10260 to 12750	 3	8.3	
Characteristic Impedance (Ω)			50 (Nomina))

• Ta: +25±5°C


TEMPERATURE RANGE

Operating temperature	Storage temperature
(°C)	(°C)
-40 to +85	-40 to +85

All specifications are subject to change without notice. Before using these products, be sure to request the delivery specifications.

DEA161910LT-9031A1

FREQUENCY CHARACTERISTICS




• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

⊗TDK

RF Components

RECOMMENDED REFLOW PROFILE



Preheating		Soldering				
		Critical zone (T3 to T4)		Peak	Peak	
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	ТЗ	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120s	ec 240 to 260°C	30sec max.

*t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.



All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

⊗TDK

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

▲ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.