
OxiCap® NLJ Series **Niobium Oxide Capacitors High CV Consumer Series**









MARKING


A, B, G, S, T CASE







HOW TO ORDER



476 **Capacitance Code** 1st two digits represent significant figures, 3rd digit represents multiplier in pF



CASE DIMENSIONS:

EIA

Metric

3216-18

3528-21

3216-15

2012-15

3216-12

3528-12

EIA

Code

1206

1210

1206

0805

1206

1210

Code

Δ


в


G

Ρ

s

т





TECHNICAL SPECIFICATIONS

Technical Data:	cal Data:				All technical data relate to an ambient temperature of +25°C						
Capacitance Range:		22 μF to 150 μF									
Capacitance Tolerance:		±20%									
Leakage Current DCL:		0.1CV									
Rated Voltage (V _R)	-55°C ≤ +40°C:	4	6.3	10							
Category Voltage (V_c)	at 85°C:	2	3.2	5							
Category Voltage (V _c)	at 105°C:	1.3	2	3.3							
Temperature Range:		-55°C to	+105°C v	with cate	gory voltage						
Reliability:			r 1000 ho 6 confide		$^{\circ}$ C, 0.5xV _R , 0.1 Ω /V series impedance						



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

FEATURES

- High Volumetric Efficiency
- **Environmentally Friendly** .
- 3x Reflow 260°C Compatible 100% Surge Current Tested
- **Consumer Applications** .
- OxiCap[®] Non-Burn Technology
- **RoHS** Compliance
- Lead-Free Solution .
- 6 Case Sizes Available .
- CV Range: 22-150µF / 4-10V

APPLICATIONS

L±0.20

(0.008)

3.20 (0.126)

3.50 (0.138)

3.20 (0.126)

2.05 (0.081)

3.20 (0.126)

3.50 (0.138)

· Consumer Handhelds and Entertainment

W+0.20 (0.008) -0.10 (0.004)

1.60 (0.063)

2.80 (0.110)

1.60 (0.063)

1.35 (0.053)

1.60 (0.063)

2.80 (0.110)

H+0.20 (0.008) -0.10 (0.004)

1.60 (0.063)

1.90 (0.075)

1.50 (0.059) max

1.50 (0.059) max

1.20 (0.047) max

1.20 (0.047) max

 W_1 dimension applies to the termination width for A dimensional area only.



LEAD-FREE COMPATIBLE COMPONENT



RoHS COMPLIANI Elektra Award 2005

S Min.

1.10 (0.043)

1.40 (0.055)

1.10 (0.043)

0.85 (0.033)

1.10 (0.043)

1.40 (0.055)

NON-BURN NON-SMOKE

W₁ ±0.20 (0.008)

1.20 (0.047)

2.20 (0.087)

1.20 (0.047)

1.00±0.10

(0.039±0.004)

1.20 (0.047)

2.20 (0.087)

A+0.30 (0.012) -0.20 (0.008)

0.80 (0.031)

0.80 (0.031)

0.80 (0.031)

0.50 (0.020)

0.80 (0.031)

0.80 (0.031)

millimeters (inches)

1	7



CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capaci	itance	R	Rated Voltage DC to 40°C					
μF	Code	4V (G)	6.3V (J)	10V (A)				
22	226	P(4000)	S(1800)	A(4000)/G(3000)				
33	336		G(2200)	A(1700)				
47	476		A(1600)/T(1600)	B(1000)				
68	686							
100	107		B(1700)					
150	157	B(1500)						

Released ratings, (ESR ratings in mOhms in parentheses)

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher voltage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

AVX	Case Capacitance Size (µF)	Rated	Rated	Category	Category	Maximum	DCL	ESR Max.	100kHz RMS Current (mA)				
Part No.			Voltage (V)	Temperature (°C)	Voltage (V)	Temperature (°C)	Surge Current (A)	Мах. (µА)	@100kHz (mΩ)	25°C	85°C	105°C	MSL
4 Volt @ 85°C													
NLJP226M004#4000	P	22	4	85	1.3	105	0.4	8.8	4000	134	121	54	3
NLJB157M004#1500	В	150	4	85	1.3	105	1.0	60.0	1500	261	235	104	3
					6.3 V	olt @ 85°C							
NLJS226M006#1800	S	22	6.3	85	2	105	1.4	13.2	1800	208	187	83	3
NLJG336M006#2200	G	33	6.3	85	2	105	1.2	19.8	2200	195	176	78	3
NLJA476M006#1600	A	47	6.3	85	2	105	1.5	28.2	1600	237	213	98	3
NLJT476M006#1600	Т	47	6.3	85	2	105	1.5	28.2	1600	245	220	98	3
NLJB107M006#1700	B	100	6.3	85	2	105	1.5	60.0	1700	245	220	98	3
10 Volt @ 85°C													
NLJA226M010#4000	A	22	10	85	3.3	105	1.1	22.0	4000	150	135	60	3
NLJG226M010#3000	G	22	10	85	3.3	105	1.4	22.0	3000	167	151	67	3
NLJA336M010#1700	A	33	10	85	3.3	105	2.3	33.0	1700	230	207	92	3
NLJB476M010#1000	В	47	10	85	3.3	105	3.4	47.0	1000	319	287	128	3

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V

RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.


ESR allowed to move up to 1.25 times catalogue limit post mounting

DCL allowed to move up to 2.00 times catalogue limit post mounting

For typical weight and composition see page 274.

NOTE: AVX reserves the right to supply higher voltage ratings or tighter tolerance part in the same case size, to the same reliability standards.





OxiCap® NLJ Series



Niobium Oxide Capacitors High CV Consumer Series

QUALIFICATION TABLE

TEST	NLJ series (Temperature range -55°C to +105°C)											
IESI		Condition	Characteristics									
Apply rated voltage (Ur) at 40°C and / or category				Visual examination	/isual examination no visible damage							
		°C for 2000 hours th	DCL	2 x initial	2 x initial limit							
Endurance	impedance of ≤0.	1Ω/V. Stabilize at roo		ΔC/C	within ±1	within ±10% of initial value						
	for 1-2 hours before measuring.			ESR	1.25 x ini	1.25 x initial limit						
	Store at 65°C and	Visual examination	no visible damage									
Humidity	hours, with no app	olied voltage. Stabiliz	e at room	DCL	2 x initial limit							
пишицу	temperature and h	numidity for 1-2 hour	s before	ΔC/C	within ±1	within ±10% of initial value						
	measuring.			ESR	1.25 x ini	1.25 x initial limit						
	Step 1	Temperature°C +20	Duration(min) 15	_	+20°C	-55°C	+20°C	+85°C	+105°C	+20°C		
Temperature	2	-55	15	DCL	2 x IL*	n/a	2 x IL**	10 x IL*	12.5 x IL*	2xIL*		
Stability	3 4	+20 +85	15 15		n/a	+0/-20%	±5%	+20/-0%	+25/-0%	±5%		
	5	+105	15	ESR	1.25 x IL*	2.5 x IL*	1.25 x IL*		-	1.25 x IL*		
	6	+20	15	-	-	-	1.25 X IL^	1.25 X IL^	1.25 X IL^	1.23 X IL^		
	Apply 1 Overstady	altana (Lir) at 4000 f	Visual examination	no visible damage								
Surge	Apply 1.3x rated voltage (Ur) at 40°C for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge)			DCL	2 x initial	2 x initial limit						
Voltage		/ discharge resistand	ΔC/C	within ±5	within ±5% of initial value							
	5 5	5	ESR	1.25 x initial limit								
					no visible damage							
Mechanical	MIL-STD-202, Method 213, Condition C			DCL	initial lin	initial limit						
Shock				ΔC/C	within ±	within ±5% of initial value						
SHOCK				DF	initial lin	initial limit						
			ESR	initial lin	initial limit							
			Visual examination	no visible damage								
		MIL-STD-202, Method 204, Condition D			initial lin	initial limit						
Vibration	MIL-STD-202, Met				within ±	within ±5% of initial value						
	-			DF	initial limit							
				ESR	initial limit							

*Initial Limit




040320

OxiCap® NLJ Series

Niobium Oxide Capacitors High CV Consumer Series


AVX SOLID ELECTROLYTIC CAPACITOR ROADMAP



FIVE CAPACITOR CONSTRUCTION STYLES



SERIES LINE UP : NIOBIUM OXIDE OxiCap® CAPACITORS



182

The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

