



Dimensions: [mm]













Product Marking:

Pin 1	•
Marking	102 (Impedance Code)

Recommended Land Pattern: [mm]



Schematic:



Electrical Properties:

Properties	Test conditions		Value	Unit	Tol.
Inductance	100 kHz/ 0.1 mA	L	2x11	μΗ	typ.
Impedance	100 MHz	Z	1000	Ω	±25%
Rated Current	ΔT = 40 K	I _R	2500	mA	max.
DC Resistance		R _{DC}	2x0.03	Ω	max.
Leakage Inductance	1 MHz/ 1 mA	L _S	1300	nH	typ.
Insulation Test Voltage		U _T	500	V (AC)	max.
Rated Voltage		U_R	80	V	

General Properties:

It is recommended that the temperature of the component does not exceed +125°C under worst case conditions

Ambient Temperature (refering to $I_{\rm R}$)	-40 °C up to +85 °C							
Operating Temperature	-40 °C up to +125 °C							
Storage Temperature (in original packaging)	-20°C up to +40°C, 75% RH max.							
T 1 199 (51 1) 10 19 0000 0000 DU16 1 197 19								

Test conditions of Electrical Properties: +20°C, 33% RH if not specified differently

Würth	Elektronik	eiSos	GmbH	&	Co.	ΚŒ
FMC 8	Inductive	Soluti	ons			

Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0

www.we-online.com eiSos@we-online.com



CREATED	CHECKED	GENERAL TOLERANCE	PROJECTION METHOD	
KaS	SBa	DIN ISO 2768-1m	- [-]	
			l i l	

WE-SL5 HC SMD Common Mode Line Filter

STATUS

Valid

REVISION

002.012


ORDER CODE
744273102

DATE (YYYY-MM-DD)
2015-08-06


BUSINESS UNIT
PAGE
1/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Worth Elektronik elSos GmbH & Co KG must be informed in every electronic component with in such in a reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Worth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.


Typical Impedance Characteristics:



Test Setup:



Common Mode



Differential Mode

Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions

Max-Eyth-Str. 1 74638 Waldenburg

Tel. +49 (0) 79 42 945 - 0

www.we-online.com eiSos@we-online.com **WÜRTH ELEKTRONİK**

DESCRIPTION				,	
KaS	SBa	DIN ISO 2768-1m	I — - 		
CREATED	CHECKED	GENERAL TOLERANCE	PROJECTION METHOD	7	


WE-SL5 HC SMD Common Mode Line Filter


744273102


DATE (YYYY-MM-DD) BUSINESS UNIT REVISION STATUS PAGE 002.012 Valid 2/6 2015-08-06 eiSos


ORDER CODE


Packaging Specification - Tape and Reel: [mm]














		Α	В	C	D	N	W1	W2	W3	W3
tolerance		± 2,0	min.	min.	min.	min.	+ 2	max.	min.	max.
Tape width	16 mm	330.00	1.50	12.80	20.20	60.00	16.40	22.40	15.90	19.40

packaging is reffered to the international standard IEC 60286-3:2013

	A0	B0	W	P1	T	T1	T2	D0	E1	E2	F	P0	P2	Таре	VPE / packaging unit
tolerance	typ.	typ.	+0,3/ -0,1	±0,1	±0,1	max.	typ.	+0,3/ -0,0	±0,1	min.	±0,05	±0,1	±0,05		pcs.
ciza	8.50	10.00	16.00	12.00	0.50	0.10	6.40	1.50	1 75	1/1/25	7.50	4.00	2.00	Polystyrene	1000



Pull-of force 16 mm Tape width 0,1 N - 1,3 N Würth Elektronik eiSos GmbH & Co. KG **EMC & Inductive Solutions** Max-Eyth-Str. 1

74638 Waldenburg Tel. +49 (0) 79 42 945 - 0

www.we-online.com eiSos@we-online.com WÜRTH ELEKTRONIK

CREATED

KaS

GENERAL TOLERANCE CHECKED SBa DIN ISO 2768-1m

Line Filter


WE-SL5 HC SMD Common Mode

744273102 DATE (YYYY-MM-DD) BUSINESS UNIT

REVISION STATUS PAGE 002.012 2015-08-06 3/6 Valid eiSos

ORDER CODE

Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

Profile Feature		Value
Preheat Temperature Min	T _{s min}	150 °C
Preheat Temperature Max	T _{s max}	200 °C
Preheat Time t_s from $T_{s min}$ to $T_{s max}$	t _s	60 - 120 seconds
Ramp-up Rate (T _L to T _P)		3 °C/ second max.
Liquidous Temperature	T _L	217 °C
Time t_L maintained above T_L	t _L	60 - 150 seconds
Peak package body temperature	T _p	see table below
Time within 5°C of actual peak temperaure	t _p	20 - 30 seconds
Ramp-down Rate (T _L to T _P)		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature:

	Properties	Volume mm³ <350	Volume mm ³ 350-2000	Volume mm³ >2000
	PB-Free Assembly Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
I	PB-Free Assembly I Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
	PB-Free Assembly I Package Thickness ≥ 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

GENERAL TOLERANCE CREATED CHECKED Würth Elektronik eiSos GmbH & Co. KG **EMC & Inductive Solutions** KaS SBa DIN ISO 2768-1m Max-Eyth-Str. 1 74638 Waldenburg **WE-SL5 HC SMD Common Mode** Tel. +49 (0) 79 42 945 - 0 **Line Filter** ORDER CODE www.we-online.com 744273102 eiSos@we-online.com DATE (YYYY-MM-DD) BUSINESS UNIT REVISION STATUS PAGE 002.012 Valid 2015-08-06 4/6 eiSos WÜRTH ELEKTRONIK

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-SL5 HC of Würth Elektronik eiSos GmbH & Co. KG:

General:

All recommendations according to the general technical specifications of the data sheet have to be complied with.

The usage and operation of the product within ambient conditions, which probably alloy or harm the wire isolation, has to be avoided.

If the product is potted in customer applications, the potting material might shrink during and after hardening. The product is exposed to the pressure of the potting material with the effect that the core, wire and termination is possibly damaged by this pressure and so the electrical as well as the mechanical characteristics are endangered to be affected. After the potting material is cured, the core, wire and termination of the product have to be checked if any reduced electrical or mechanical functions or destructions have occurred.

The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.

Cleaning agents that are used to clean the customer application might damage or change the characteristics of the component, body or termination.

Direct mechanical impact to the product shall be prevented as the ferrite material of the core could flake or in the worst case it could break.

Product specific:

Follow all instructions mentioned in the data sheet, especially:

- The soldering profile has to be complied with according to the technical reflow soldering specification, otherwise this will void the
 warranty.
- All products shall be used before the end of the period of 12 months based on the product date code, if not a 100% solderability can't
 be ensured.
- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.

The general and prodcut specific cautions comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable; however, no responsibility is assumed for inaccuracies or incompleteness.



Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

