

# **TCS3707** ALS/Color Sensor with Flicker Detection

### **General Description**

The TCS3707 features ambient light and color (RGB) sensing, proximity and flicker detection. The device comes in a low-profile and small footprint, L2.5mm x W2.0mm x H0.5mm package.

The Ambient Light and Color Sensing function provides five concurrent ambient light sensing channels: Red, Green, Blue, Clear, and Wideband. The RGB and Clear channels have a UV/IR blocking filter. This architecture accurately measures ambient light and enables the calculation of illuminance, chromaticity, and color temperature to manage display appearance. The device integrates direct detection of 50Hz or 60Hz ambient light flicker. Flicker detection is executed in parallel with ambient light and color sensing and has independent gain configuration. The flicker detection engine can also buffer data for calculating other flicker frequencies externally.



## Key Benefits & Features

The benefits and features of TCS3707 are listed below:

Figure 1:

Added Value of Using TCS3707

| Benefits   | Features   |
|--|--|
| • Invisible ALS and color sensing under any glass type                       | <ul> <li>Configurable, high sensitivity         <ul> <li>Programmable gain and integration time</li> <li>1024x dynamic range by gain adjustment only</li> <li>1mlux minimum detectable illuminance (100ms)</li> </ul> </li> <li>Tailored ALS and color response         <ul> <li>UV/IR blocking filter for RGBC channels</li> <li>Wideband reference channel without filters</li> </ul> </li> <li>ALS/color interrupt with thresholds</li> </ul> |
| Unique fast ALS integration mode   | Flicker-immune ALS sensing within 10ms   |
| Integrated ambient light flicker detection on chip                           | <ul> <li>Independently configurable timing and gain</li> <li>Automatic gain adjustment</li> <li>50Hz and 60Hz flicker detection flags</li> <li>Flicker detected interrupt</li> </ul>   |
| <ul> <li>Low power consumption and minimum I<sup>2</sup>C traffic</li> </ul> | <ul> <li>1.8V<sub>DD</sub> operation</li> <li>Configurable sleep mode</li> <li>Interrupt-driven device</li> <li>On-chip self-calibration of ALS and proximity functions</li> </ul>   |
| Integrated status checking for all functions                                 | <ul> <li>Digital and analog ALS saturation flags</li> <li>Proximity saturation flag</li> </ul>   |

# Applications

TCS3707 integrates multiple applications within one device. The applications for TCS3707 include:


- Brightness management for displays
- Color management for displays
- Camera image processing
- Flicker-immune camera operation
- Touch screen disable



# **Block Diagram**

The functional blocks of this device are shown below:

Figure 2: Functional Blocks of TCS3707



### **Copyrights & Disclaimer**

Copyright ams AG, Tobelbader Strasse 30, 8141 Premstaetten, Austria-Europe. Trademarks Registered. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner.

Devices sold by ams AG are covered by the warranty and patent indemnification provisions appearing in its General Terms of Trade. ams AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein. ams AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with ams AG for current information. This product is intended for use in commercial applications. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or life-sustaining equipment are specifically not recommended without additional processing by ams AG for each application. This product is provided by ams AG "AS IS" and any express or implied warranties, including, but not limited to the implied warranties of merchantability and fitness for a particular purpose are disclaimed.

ams AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein. No obligation or liability to recipient or any third party shall arise or flow out of ams AG rendering of technical or other services.

#### **Contact Information**

Buy our products or get free samples online at: www.ams.com/Products

Technical Support is available at: www.ams.com/Technical-Support

Provide feedback about this document at: www.ams.com/Document-Feedback

For further information and requests, e-mail us at: ams\_sales@ams.com

For sales offices, distributors and representatives, please visit: www.ams.com/Contact

#### Headquarters

ams AG Tobelbader Strasse 30 8141 Premstaetten Austria, Europe

Tel: +43 (0) 3136 500 0 Website: www.ams.com