

August 2016

## **Multilayer** Diplexer

For 2400-2500MHz / 5150-5850MHz

# DPX105850DT-6018A1

1.0x0.5mm [EIA 0402]\*

\* Dimensions Code JIS[EIA]

### **Multilayer Diplexer**


**Conformity to RoHS Directive** 


**公TDK** 

For 2400-2500MHz / 5150-5850MHz

# DPX105850DT-6018A1

### SHAPES AND DIMENSIONS






minal functions
Common
GND
High-band
Low-band


Dimensions in mm

### RECOMMENDED LAND PATTERN



Dimensions in mm

### EVALUATION BOARD



Line width should be designed to match  $50\Omega$  characteristic impedance, depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

· All specifications are subject to change without notice.

### DPX105850DT-6018A1

### ELECTRICAL CHARACTERISTICS

#### LOW-BAND

ltem	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	2400 to 2500	—	0.33	0.50
Return Loss (dB)	2400 to 2500	10	17	—
Attenuation (dB)	4800 to 6000	17	27	—
	7200 to 7500	15	33	_
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

#### HIGH-BAND

ltem	Frequency Rang (MHz)	je Min.	Тур.	Max.
Insertion Loss (dB)	5150 to 5850	—	0.86	1.40
Return Loss (dB)	5150 to 5850	10	14	—
Attenuation (dB)	700 to 2025	25	32	_
	2400 to 2690	25	30	_
	3500 to 3700	3	6	—
	7250 to 7800	7	9	_
	10300 to 11700	20	27	_
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

#### 

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Return Loss (dB)	2400 to 2500	10	15	—
	5150 to 5850	10	14	—
Characteristic Impedance (Q)			50 (Nominal)	

• Ta: +25±5°C

#### **TEMPERATURE RANGE**


Operating temperature	Storage temperature
(°C)	(°C)
-40 to +85	-40 to +85

• All specifications are subject to change without notice.


### DPX105850DT-6018A1

### FREQUENCY CHARACTERISTICS


#### LOW-BAND




**Return Loss** 











**Return Loss** 

**HIGH-BAND** 



Attenuation





• All specifications are subject to change without notice.

### DPX105850DT-6018A1

### FREQUENCY CHARACTERISTICS

#### 






• All specifications are subject to change without notice.

### **⊗TDK**

### RECOMMENDED REFLOW PROFILE



Soldering Preheating Critical zone (T3 to T4) Peak Temp. Time Temp. Time Temp. Time T1 Т2 **T**4 t3\* t1 ТЗ t2 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30sec max.

 $^{\ast}$  t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

### **REMINDERS FOR USING THESE PRODUCTS**

Before using these products, be sure to request the delivery specifications.

### SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

### **▲** REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

```
• Before using these products, be sure to request the delivery specifications.
```