

April 2019

Multilayer Diplexer

For 698-2690MHz / 3400-5850MHz

DPX165850DT-8086A1

1.6x0.8mm [EIA 0603]*


* Dimensions Code JIS[EIA]

Multilayer Diplexer

For 698-2690MHz / 3400-5850MHz

DPX165850DT-8086A1


SHAPES AND DIMENSIONS



Dimensions in mm


Те	Terminal functions			
1	GND			
2	Common Port			
3	GND			
4	High-Band Port			
5 6	GND			
6	Low-Band Port			

RECOMMENDED LAND PATTERN



Dimensions in mm

EVALUATION BOARD



material, Layer	THICKIESS
Top resist	Resist
Copper Surface Pattern	0.035mm
FR-4	0.10mm
Copper Inner GND	0.018mm
FR-4	0.30mm
Copper Bottom GND	0.035mm

Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

· All specifications are subject to change without notice.

· Before using these products, be sure to request the delivery specifications.

公TDK

ELECTRICAL CHARACTERISTICS

LOW-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	698 to 2690	—	0.66	0.80
Insertion Loss (uB)	698 to 2690	—	—	0.91 (-40 to +85°C)
Return Loss (dB)	698 to 2690	9.54	18.2	—
Attenuation (dP)	3400 to 3800	13	16.4	—
Attenuation (dB)	5150 to 5850	20	23.8	_
Power Handling (W)		_	_	2.0
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

□HIGH-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
	3400 to 3800	_	0.77	0.89
Insertion Loss (dB)	5150 to 5850	—	0.45	0.54
Insertion Loss (ub)	3400 to 3800	—	—	0.96 (–40 to +85°C)
	5150 to 5850	—	—	0.64 (–40 to +85°C)
Deturn Loop (dP)	3400 to 3800	9.54	19.4	—
Return Loss (dB)	5150 to 5850	9.54	21.2	—
Attenuetion (dP)	698 to 2690	14	16.6	—
Attenuation (dB)	10300 to 11700	18	23.4	_
Power Handling (W)		—	—	2.0
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

Item	Frequency Range (MHz)	Min.	Тур.	Max.
	698 to 2690	14	15.8	
Isolation (dB)	3400 to 3800	13	16.6	_
	5150 to 5850	20	23.6	_
	698 to 2690	9.54	16.8	_
Return Loss (dB)	3400 to 3800	9.54	20.1	_
	5150 to 5850	9.54	22.1	_
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

TEMPERATURE RANGE


Operating temperature	Storage temperature
(°C)	(°C)
-40 to +85	-40 to +85

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.


DPX165850DT-8086A1

FREQUENCY CHARACTERISTICS






Return Loss




Attenuation







Insertion Loss



Return Loss



Attenuation




• All specifications are subject to change without notice.


• Before using these products, be sure to request the delivery specifications.

DPX165850DT-8086A1

FREQUENCY CHARACTERISTICS



Isolation




⊗TDK

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

DPX165850DT-8086A1

RECOMMENDED REFLOW PROFILE



Preheating			Soldering Critical zone (T3 to T4) Peak			
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	Т3	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30sec max.

*t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.