

#### Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <a href="http://www.nxp.com">http://www.nxp.com</a>, <a href="http://www.semiconductors.philips.com/">http://www.nxp.com</a>, <a href="http://www.nexperia.com/">http://www.nexperia.com/</a>, <a href="http://www.nexperia.com/">http://www.nexperia.com/</a>, <a href="http://www.nexperia.com/">use http://www.nexperia.com/</a>

Instead of sales.addresses@www.nxp.com or sales.addresses@www.semiconductors.philips.com, use salesaddresses@nexperia.com (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © Nexperia B.V. (year). All rights reserved.


If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **salesaddresses@nexperia.com**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

### **DISCRETE SEMICONDUCTORS**

# DATA SHEET



### BAS29; BAS31; BAS35 General purpose controlled avalanche (double) diodes

Product data sheet Supersedes data of 2001 Oct 10 2003 Mar 20



## General purpose controlled avalanche (double) diodes

**BAS29**; **BAS31**; **BAS35** 

#### **FEATURES**

• Small plastic SMD package

• Switching speed: max. 50 ns

· General application

• Continuous reverse voltage: max. 90 V

• Repetitive peak reverse voltage: max. 110 V

· Repetitive peak forward current: max. 600 mA

• Repetitive peak reverse current: max. 600 mA.

#### **APPLICATIONS**

General purpose switching in e.g. surface mounted circuits.

#### **DESCRIPTION**

General purpose switching diodes fabricated in planar technology, and encapsulated in small rectangular plastic SMD SOT23 packages. The BAS29 consists of a single diode. The BAS31 has two diodes in series. The BAS35 has two diodes with a common anode.

#### **MARKING**


TYPE NUMBER	MARKING CODE(1)
BAS29	L20 or *A8
BAS31	L21 or *V1
BAS35	L22 or *V2

#### Note

\* = p : Made in Hong Kong.
\* = t : Made in Malaysia.
\* = W : Made in China.

#### **PINNING**

PIN	DESCRIPTION			
FIN			BAS35	
1	anode	anode	cathode (k1)	
2	not connected	cathode	cathode (k2)	
3	cathode	common connection	common anode	



rig. i Simplified outline (50125) and symbols

# General purpose controlled avalanche (double) diodes

BAS29; BAS31; BAS35

#### **LIMITING VALUES**

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
Per diode					
$V_{RRM}$	repetitive peak reverse voltage		_	110	V
$V_R$	continuous reverse voltage		_	90	V
I <sub>F</sub>	continuous forward current	single diode loaded; see Fig.2; note 1	_	250	mA
		double diode loaded; see Fig.2; note 1	_	150	mA
I <sub>FRM</sub>	repetitive peak forward current		_	600	mA
I <sub>FSM</sub>	non-repetitive peak forward current	square wave; T <sub>j</sub> = 25 °C prior to surge; see Fig.4			
		t = 1 μs	_	10	Α
		t = 100 μs	_	4	Α
		t = 1 s	_	0.75	Α
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = 25 °C; note 1	_	250	mW
I <sub>RRM</sub>	repetitive peak reverse current		_	600	mA
E <sub>RRM</sub>	repetitive peak reverse energy	$t_p \ge 50 \ \mu s; \ f \le 20 \ Hz; \ T_j = 25 \ ^{\circ}C$	_	5	mJ
T <sub>stg</sub>	storage temperature		-65	+150	°C
Tj	junction temperature		_	150	°C

#### Note

<sup>1.</sup> Device mounted on an FR4 printed-circuit board.

# General purpose controlled avalanche (double) diodes

BAS29; BAS31; BAS35

#### **ELECTRICAL CHARACTERISTICS**

 $T_j = 25$  °C unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
Per diode					
V <sub>F</sub>	forward voltage	see Fig.3			
		I <sub>F</sub> = 10 mA	_	750	mV
		I <sub>F</sub> = 50 mA	_	840	mV
		I <sub>F</sub> = 100 mA	_	900	mV
		I <sub>F</sub> = 200 mA	_	1	V
		I <sub>F</sub> = 400 mA	_	1.25	V
I <sub>R</sub>	reverse current	see Fig.5			
		V <sub>R</sub> = 90 V	_	100	nA
		V <sub>R</sub> = 90 V; T <sub>j</sub> = 150 °C	_	100	μΑ
V <sub>(BR)R</sub>	reverse avalanche breakdown voltage	I <sub>R</sub> = 1 mA	120	170	V
C <sub>d</sub>	diode capacitance	$f = 1 \text{ MHz}; V_R = 0; \text{ see Fig.6}$	_	35	pF
t <sub>rr</sub>	reverse recovery time	when switched from $I_F$ = 30 mA to $I_R$ = 30 mA; $R_L$ = 100 $\Omega$ ; measured at $I_R$ = 3 mA; see Fig.7	_	50	ns

#### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
R <sub>th j-tp</sub>	thermal resistance from junction to tie-point		360	K/W
R <sub>th j-a</sub>	thermal resistance from junction to ambient	note 1	500	K/W

#### Note


1. Device mounted on an FR4 printed-circuit board.

2003 Mar 20

### General purpose controlled avalanche (double) diodes

BAS29; BAS31; BAS35


#### **GRAPHICAL DATA**



Device mounted on an FR4 printed-circuit board.

- (1) Single diode loaded.
- (2) Double diode loaded.

Fig.2 Maximum permissible continuous forward current as a function of ambient temperature.



- (1)  $T_j = 150 \,^{\circ}\text{C}$ ; typical values.
- (2)  $T_j = 25$  °C; typical values.
- (3)  $T_j = 25$  °C; maximum values.

Fig.3 Forward current as a function of forward voltage.






Fig.4 Maximum permissible non-repetitive peak forward current as a function of pulse duration.


2003 Mar 20 5

# General purpose controlled avalanche (double) diodes

BAS29; BAS31; BAS35








# General purpose controlled avalanche (double) diodes

BAS29; BAS31; BAS35

#### **PACKAGE OUTLINE**

Plastic surface mounted package; 3 leads

SOT23



OUTLINE	REFERENCES			EUROPEAN	ISSUE DATE	
VERSION	IEC	JEDEC	EIAJ		PROJECTION	ISSUE DATE
SOT23		TO-236AB				<del>97-02-28</del> 99-09-13

0.95

0.45

0.15

0.55

0.45

0.1

2003 Mar 20 7

0.48

0.38

0.1

mm

0.15

0.09

3.0

2.8

1.4

1.9

### General purpose controlled avalanche (double) diodes

BAS29; BAS31; BAS35

#### **DATA SHEET STATUS**

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

#### **Notes**

- 1. Please consult the most recently issued document before initiating or completing a design.
- 2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### **DISCLAIMERS**

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings

System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

### **NXP Semiconductors**

#### **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors. No changes were made to the content, except for the legal definitions and disclaimers.

#### **Contact information**

For additional information please visit: http://www.nxp.com

For sales offices addresses send e-mail to: salesaddresses@nxp.com

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands 613514/05/pp9 Date of release: 2003 Mar 20 Document order number: 9397 750 10962

