

July 2015

Multilayer Diplexer

For 704-960MHz / 1710-2690MHz

DPX202690DT-4049A2

2.0x1.25mm [EIA 0805]*

* Dimensions Code JIS[EIA]

Multilayer Diplexer


Conformity to RoHS Directive


公TDK

For 704-960MHz / 1710-2690MHz

DPX202690DT-4049A2

SHAPES AND DIMENSIONS






Terminal functions			
GND			
Common			
GND			
High-band			
GND			
Low-band			


Dimensions in mm

RECOMMENDED LAND PATTERN



Dimensions in mm

EVALUATION BOARD



Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/

All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

DPX202690DT-4049A2

ELECTRICAL CHARACTERISTICS

LOW-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	704 to 960	—	0.24	0.30
Return Loss (dB)	704 to 824	11.73	18.0	—
	824 to 960	13.98	19.7	_
Attenuation (dB)	1710 to 2170	15	17.7	_
	2170 to 2690	13	16.8	_
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

HIGH-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.	
Incortion Loop (dR)	1710 to 2170	—	0.38	0.50	
Insertion Loss (dB)	2170 to 2690	—	0.83	1.20	
	1710 to 2170	11.73	13.8	—	
Return Loss (dB)	2170 to 2690	7.36	8.8	—	
Attenuation (dB) 704 to 824 824 to 960	704 to 824	17	20.4	—	
	824 to 960	20	22.8	—	
Characteristic Impedance (Ω)			50 (Nominal)		

• Ta: +25±5°C

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Return Loss (dB)	704 to 824	11.73	17.5	
	824 to 960	13.98	19.4	
	1710 to 2170	11.73	13.6	
	2170 to 2690	7.36	8.8	
Power Handling (W)		_	_	3
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

TEMPERATURE RANGE


Operating temperature	Storage temperature
(°C)	(°C)
-40 to +85	-40 to +85

[•] Before using these products, be sure to request the delivery specifications.


DPX202690DT-4049A2

FREQUENCY CHARACTERISTICS


LOW-BAND




Return Loss




Attenuation










Attenuation



• All specifications are subject to change without notice.


• Before using these products, be sure to request the delivery specifications.

DPX202690DT-4049A2

FREQUENCY CHARACTERISTICS








• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

⊗TDK

⊗TDK

RECOMMENDED REFLOW PROFILE



Soldering Preheating Critical zone (T3 to T4) Peak Temp. Time Temp. Time Temp. Time T1 T2 **T**4 t3* t1 ТЗ t2 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30sec max.

 * t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

▲ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.