MBR2045MFS, NRVB2045MFS

Switch-mode Power Rectifiers

These state-of-the-art devices have the following features:

Features

- Low Power Loss / High Efficiency
- New Package Provides Capability of Inspection and Probe After Board Mounting
- Guardring for Stress Protection
- Low Forward Voltage Drop
- 150°C Operating Junction Temperature
- Wettable Flacks Option Available
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable*
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Mechanical Characteristics:

- Case: Epoxy, Molded
- Epoxy Meets Flammability Rating UL 94–0 @ 0.125 in.
- Lead Finish: 100% Matte Sn (Tin)
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Device Meets MSL 1 Requirements

Applications

- Output Rectification in Compact Portable Consumer Applications
- Freewheeling Diode used with Inductive Loads





ORDERING INFORMATION

= Lot Traceability

ΖZ

Device	Package	Shipping†		
MBR2045MFST1G	SO-8 FL (Pb-Free)	1500 / Tape & Reel		
NRVB2045MFST1G*	SO-8 FL (Pb-Free)	1500 / Tape & Reel		
MBR2045MFST3G	SO-8 FL (Pb-Free)	5000 / Tape & Reel		
NRVB2045MFST3G*	SO–8 FL (Pb–Free)	5000 / Tape & Reel		

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

MBR2045MFS, NRVB2045MFS

MAXIMUM RATINGS

Rating	Symbol	Value	Unit	
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage	V _{RRM} V _{RWM}		V	
DC Blocking Voltage	V _R	45		
Average Rectified Forward Current (Rated V_R , T_C = 130°C)	I _{F(AV)}	20	A	
Peak Repetitive Forward Current, (Rated V _R , Square Wave, 20 kHz, T _C = 135°C)	I _{FRM}	40	A	
Non–Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)	I _{FSM}	400	A	
Storage Temperature Range	T _{stg}	-65 to +175	°C	
Operating Junction Temperature	TJ	-55 to +150	°C	
Unclamped Inductive Switching Energy (10 mH Inductor, Non-repetitive)	E _{AS}	150	mJ	
ESD Rating (Human Body Model)		3B		
ESD Rating (Machine Model)		M4		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

NOTE: The heat generated must be less than the thermal conductivity from Junction-to-Ambient: dPD/dTJ < 1/RJA

THERMAL CHARACTERISTICS

Characteristic	Symbol	Тур	Max	Unit
Thermal Resistance, Junction-to-Case, Steady State (Assumes 600 mm ² 1 oz. copper bond pad, on a FR4 board)	$R_{ extsf{ heta}JC}$	-	1.6	°C/W
Thermal Resistance, Junction-to-Ambient, Steady State (Assumes 600 mm ² , 2-oz, 2 layer on a FR4 board)	R _{θJA}	-	45	°C/W


ELECTRICAL CHARACTERISTICS

Instantaneous Forward Voltage (Note 1) ($i_F = 15 \text{ A}, T_J = 125^{\circ}\text{C}$) ($i_F = 15 \text{ A}, T_J = 25^{\circ}\text{C}$) ($i_F = 30 \text{ A}, T_J = 125^{\circ}\text{C}$) ($i_F = 30 \text{ A}, T_J = 25^{\circ}\text{C}$)	VF	0.35 0.44 0.46 0.51	0.41 0.49 0.58 0.61	V
Instantaneous Reverse Current (Note 1) (Rated dc Voltage, $T_J = 125^{\circ}C$) (Rated dc Voltage, $T_J = 25^{\circ}C$)	iR	200 0.3	300 0.6	mA

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 1. Pulse Test: Pulse Width = $300 \ \mu$ s, Duty Cycle $\leq 2.0\%$.


MBR2045MFS, NRVB2045MFS

TYPICAL CHARACTERISTICS



MBR2045MFS, NRVB2045MFS

TYPICAL CHARACTERISTICS



PULSE TIME (sec) **Figure 8. Thermal Response**

0.1

0.01

1

0.001

0.0001

R(t) (°C/W)

0.001

Single Pulse

0.000001

0.00001

1000

10

100





ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative