



MGPWL-00057-P	REV	
1879483-1	BA	
Product Description	IND SDRI 6.8X2.8mm SMD SS Previously MGPWL-00057	



Primary Units are in inches millimetres in brackets

Electrical Specifications at +20°C unless noted otherwise

Test	Limits	Unit	Tol	Notes
Inductance	220	µH	±10%	1-2, 100kHz, 100mVAC, Ls.
Saturation current	1.60	A	Max.	applied to produce a typical 10% decrease in nominal Ls.
DC Resistance	0.230	Ω	Max.	Pins 1 - 2
Dielectric	50	VDC	500µA	1-CORE, 1 second test, 500µA maximum leakage current.

Terminal Plating is Hot-dipped SnAgCu
260°C Maximum reflow solder temperature per J-STD-020
Operating Temperature range -40°C to +85°C



The information contained in this drawing is the sole property of Tyco Electronics. Any reproduction or use without the written permission of Tyco Electronics is prohibited.

Specifications subject to change without notice. For latest revision visit <http://www.tycoelectronics.com>