

REV. 0


DCO 143545

COIL: @ 25°C	
RESISTANCE	63 OHMS ±10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	3.0 VDC
TURN-ON BASE CURRENT	0.60 mADC
MUST RELEASE	1.7 VDC MAX, 0.24 VDC MIN.

ENVIRONMENT:			
VIBRATION	10	CPS TO	3000
		CPS @	30
		g's	
SHOCK	75	g's	6
		MS. DURATION	
TEMPERATURE	-65	°C TO	+125
		°C	

NOTES:	TURN-ON TIME 2.0 MS MAX.
	TURN-OFF TIME 7.5 MS MAX.
	CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 06MAY02

Handwritten signature and date: 5/6/02

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M28776/5-013L REV.

"J1MAT" RELAY

J1MAWT-5XL