

Feb.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD							
RATING	FREQUENCY RANGE	$\triangle$ DC ~ 67 GHz	STORAGE TEMPERATURE RANGE	-55°C ~ + 125°C (No Load) (※1)			
	POWER	1 W CW (AT 65°C)	CHARACTERISTIC IMPEDANCE	50 $\Omega$			
	OPERATING TEMPERATURE RANGE	-10 °C TO +65 °C	APPLICABLE CABLE	---			
	OPERATING RELATIVE HUMIDITY	~ 90 %	USED CONNECTOR	HV-P , HV-J			
SPECIFICATIONS							
ITEM	TEST METHOD		REQUIREMENTS	QT	AT		
CONSTRUCTION							
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X		
MARKING	CONFIRMED VISUALLY.			X	X		
ELECTRIC CHARACTERISTICS							
V.S.W.R	MUST BE UNDER THE STD.VALUE AT FREQUENCY DC TO 67 GHz $\triangle$		1.40 MAX (DC~40GHz) $\triangle$ 1.60 MAX (40 ~67GHz)	X	X		
INSERTION LOSS	MUST BE UNDER THE STD.VALUE AT FREQUENCY DC TO 67 GHz $\triangle$		19dB ~21dB ( DC ~18GHz)	X	X		
			19dB ~21.2dB ( 18 ~26.5GHz)				
			19dB ~21.4dB ( 26.5 ~40GHz)				
			$\triangle$ 19dB ~21.6dB ( 40 ~67GHz)				
INSULATION RESISTANCE	MUST BE OVER STANDARD VALUE AT DC V.		MINIMUM OF M $\Omega$	-	-		
VOLTAGE PROOF	V AC FOR 1 min.CURRENT LEAKAGE 2mA MAX.		NO FLASHOVER OR BREAKDOWN.	-	-		
RESISTANCE VALUE	MEASURE THE RESISTANCE VALUE AT DC V.		MAX	-	-		
MECHANICAL CHARACTERISTICS							
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO DAMAGE, CRACK, AND LOOSENESS, OF PARTS.	X	-		
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm OR 1 oct/min AT 10 CYCLES FOR 3 DIRECTIONS.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO DAMAGE, CRACK, AND LOOSENESS, OF PARTS.	X	-		
SHOCK	490 m/s <sup>2</sup> AT 18 TIMES FOR 3 DIRECTIONS.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO DAMAGE, CRACK, AND LOOSENESS, OF PARTS.	X	-		
ENVIRONMENTAL CHARACTERISTICS							
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → 15~25 → 125 → 15~25 °C TIME 30 → 2~3 → 30 → 2~3 min UNDER 100 CYCLES.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO HEAVY CORROSION.	X	-		
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 °C, 90% TO 95% TOTAL 96 h.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO HEAVY CORROSION.	X	-		
DRY HEAT	EXPOSED AT 125 °C TOTAL 48 h.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO HEAVY CORROSION.	X	-		
COLD	EXPOSED AT -55 °C TOTAL 48 h.		①ELECTRICAL CHARACTERISTIC SHALL BE MET. ②NO HEAVY CORROSION.	X	-		
CORROSION SALT MIST	EXPOSED IN 5±1 % SALT WATER , AT 35±2°C SPRAY FOR 48 HOURS.		NO HEAVY CORROSION.	X	-		
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
$\triangle$	5	DIS-D-00002210	HA. NISHIMURA	TS. NOBE	17. 06. 23		
REMARKS			APPROVED	KY. SHIMIZU	14. 12. 18		
RoHS COMPLIANT			CHECKED	TO. KATAYAMA	14. 12. 18		
High frequency performance is only measured and the data is not attached.			DESIGNED	YI. FUNADA	14. 12. 17		
(※1) The storage temperature range means the one of the product itself without packaging.			DRAWN	YI. FUNADA	14. 12. 17		
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-180473-00			
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	HV-AT (20) -PJ			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL354-0248-2-00		$\triangle$	1/1