

Series 285S/N Flange Mount Non-Contacting Position Sensor

- Compact 45 mm x 22 mm size
- Hall-effect technology
- Extended rotational life (10 Million cycles)
- Wide temperature range (-40°C to +125°C)
- Precision linearity (± 0.5% and ± 0.25% options)
- Dust & water protection (IP50, 54 and 67 options)
- Single and dual output

Applications

- Actuator motor position feedback
- Medical treatment chair and patient platform position feedback
- Flow valve position feedback

Ordering Information

- Foot pedal and twist throttle controls
- Steering and lift & shuttle controls

position feedback

RoHS

Sense

Shaft Shaft Shaft Bearing Output Operating Rotation Series Linearity **IP** Rating Termination Туре Length Trim Style Type Voltage Angle 285 S С F S В С А А 4 1 Code Spec. Code Code Spec. Code Spec. Spec. Code Spec. ±0.5% 4 IP50 А Sleeve 250 mm Ν Shaftless S 1 В ±0.25% 5 IP54 bearing wires S w/Shaft 6 IP67 Code Spec. Code Spec. 20 mm С Single analog А D 25 mm output, CW 2 3/4" Single analog Spec. Code В 3 7/8" output, CCW А 3.3V* Shaftless Ν Dual analog В 5.0V С output, CW *Available with 360° EEA Dual analog only. D output, CCW Code* Total EEA Stops Code Spec. 260° 270° 270° А Flatted (6 mm dia.) F В 320° 310° 320° Flatted (1/4" dia.) 360° N/A С 360° R Round (6 mm dia.) D 200° 125° 200 Ρ Round (1/4" dia.) *Codes A, B, and C available with shaft. Ν Shaftless Codes D available with shaftless version only.



Electrical Specifications

Sensor Function

Parameter	Condition & Remarks	Min	Typical	Max	Unit
Output	Analog				
Independent Linearity		-0.5		+0.5	%
Hysteresis	Vsup			0.2	%
Output Voltage	V _{sup}	5%		95	%
Output Overvoltage Limits		-6		+18	VDC
Output Current		-8	+1	+8	mA
Output Load		5	10		kΩ
Input Voltage		-10	5	+10	VDC
Supply Voltage Absolute Limits		-18		+18	VDC
Supply Current			10	15	mA
Resolution	12 BIT at 360°				
Dielectric Strength	1 minute			750	VDC
Insulation Resistance	500 VDC	1000			MegΩ
Electrostatic Discharge (ESD)	HBM	-4		+4	kV

Mechanical and Environmental


Parameter	Condition & Remarks	Min	Typical	Max	Unit
Operating Temperature Range		-40		+125	°C
Storage Temperature Range		-40		+140	°C
Rotational Life		10,000,000			cycles
Rotational Torque			72		gf-cm
Static Stop Strength		40			in-oz
Total Mechanical Travel					
Without Stops	360° continuous				
With End Stops	320°, 270°, 200°				
Operating Speed	120 RPM max.				
Vibration	30 Gs, 50 to 500 Hz				
Panel Nut Tightening Torque	25 in-lb maximum				
IP Rating	50, 54 or 67				
Push and Pull Shaft Strength	13.6 kgf for 10 seconds				
Soldering Condition	Maximum manual temperature, 350°C for 5 seconds				
Marking	CTS logo, part number, date code				
Packaging	Standard anti-static bulk packaging				
Weight	21 gm				


All testing is performed at room ambient conditions except as noted. Users should verify device actual performance in their specific applications This product is compliant to RoHS3 Directive 2011/65/EU & 2015/863 Amendments of Annex II on 31 March 2015. Custom and value-added options available on request. Please contact your sales representative for additional information.





Mechanical Specifications

Series 285S Flange Mount, Single Output, with Shaft










TOLERANCE UNLESS OTHERWISE SPECIFIED .X (1 PLACE) : ± 0.3 .XX (2 PLACE) : ± 0.13 ANGLE : ± 3°





DESIGNATION	COLOR	
Vs	Red	
Vout	White	
Gnd	Green	



Mechanical Specifications


Series 285N Flange Mount, Single Output, Shaftless








<u>6 X 24AWG</u>

21.6










DESIGNATION	COLOR	
Vs	Red	
Vout	White	
Gnd	Green	

TOLERANCE UNLESS OTHERWISE SPECIFIED .X (1 PLACE) : ± 0.3 .XX (2 PLACE) : ± 0.13 ANGLE : ± 3°



Mechanical Specification

Series 285S Flange Mount, Dual Output, with Shaft





TOLERANCE UNLESS OTHERW SPECIFIED .X (1 PLACE) : ± 0.3 .XX (2 PLACE) : ± 0.13 ANGLE : ± 3°




Mechanical Specification


Series 285N Flange Mount, Dual Output, Shaftless








<u>6 X 24AWG</u>












DESIGNATION	COLOR		
Vs1	Red		
Vout1	Blue		
Gnd1	Black		
Vs2	Yellow		
Vout2	White		
Gnd2	Brown		

TOLERANCE UNLESS OTHERWISE SPECIFIED .X (1 PLACE) : ± 0.3 .XX (2 PLACE) : ± 0.13 ANGLE : ± 3°




Shaft Trim Options



Electrical Specification

Series 285 Flange Mount w/Shaft Single Output Graph





Series 285 Flange Mount Shaftless Dual Output Graph

