


LXV Series

- Low impedance
- Endurance with ripple current : 2,000 to 5,000 hours at 105°C
- Solvent resistant type (see PRECAUTIONS AND GUIDELINES)
- RoHS2 Compliant
- AEC-Q200 compliant : Please contact Chemi-Con for more details, test data, information.





SPECIFICATIONS

Items	Characteristics																				
Category Temperature Range	-55 to +105°C																				
Rated Voltage Range	6.3 to 100V _{dc}																				
Capacitance Tolerance	±20% (M) (at 20°C, 120Hz)																				
Leakage Current	I=0.01CV or 3µA, whichever is greater. Where, I : Max. leakage current (µA), C : Nominal capacitance (µF), V : Rated voltage (V) (at 20°C after 2 minutes)																				
Dissipation Factor (tan δ)	<table border="1"> <tr> <td>Rated voltage (V_{dc})</td> <td>6.3V</td> <td>10V</td> <td>16V</td> <td>25V</td> <td>35V</td> <td>50V</td> <td>63V</td> <td>80V</td> <td>100V</td> </tr> <tr> <td>tan δ (Max.)</td> <td>0.22</td> <td>0.19</td> <td>0.16</td> <td>0.14</td> <td>0.12</td> <td>0.10</td> <td>0.10</td> <td>0.09</td> <td>0.08</td> </tr> </table> <p>When nominal capacitance exceeds 1,000µF, add 0.02 to the value above for each 1,000µF increase. (at 20°C, 120Hz)</p>	Rated voltage (V _{dc})	6.3V	10V	16V	25V	35V	50V	63V	80V	100V	tan δ (Max.)	0.22	0.19	0.16	0.14	0.12	0.10	0.10	0.09	0.08
Rated voltage (V _{dc})	6.3V	10V	16V	25V	35V	50V	63V	80V	100V												
tan δ (Max.)	0.22	0.19	0.16	0.14	0.12	0.10	0.10	0.09	0.08												
Low Temperature Characteristics	<table border="1"> <tr> <td>Capacitance change ΔC (-55°C /+20°C)</td> <td>0.7min.</td> </tr> <tr> <td>Max. impedance ratio (-55°C /+20°C)</td> <td>3max.(6.3V_{dc}: 4max.)</td> </tr> </table> <p>(at 120Hz)</p>	Capacitance change ΔC (-55°C /+20°C)	0.7min.	Max. impedance ratio (-55°C /+20°C)	3max.(6.3V _{dc} : 4max.)																
Capacitance change ΔC (-55°C /+20°C)	0.7min.																				
Max. impedance ratio (-55°C /+20°C)	3max.(6.3V _{dc} : 4max.)																				
Endurance	<p>The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for the specified period of time at 105°C.</p> <table border="1"> <tr> <td>Time</td> <td>φ 5 to 6.3 : 2,000hours</td> <td>φ 8 & 10: 3,000hours</td> <td>φ 12.5 to φ 18: 5,000hours</td> </tr> <tr> <td>Capacitance change</td> <td colspan="3">≤ ±20% of the initial value</td> </tr> <tr> <td>D.F. (tan δ)</td> <td colspan="3">≤ 200% of the initial specified value</td> </tr> <tr> <td>Leakage current</td> <td colspan="3">≤ The initial specified value</td> </tr> </table>	Time	φ 5 to 6.3 : 2,000hours	φ 8 & 10: 3,000hours	φ 12.5 to φ 18: 5,000hours	Capacitance change	≤ ±20% of the initial value			D.F. (tan δ)	≤ 200% of the initial specified value			Leakage current	≤ The initial specified value						
Time	φ 5 to 6.3 : 2,000hours	φ 8 & 10: 3,000hours	φ 12.5 to φ 18: 5,000hours																		
Capacitance change	≤ ±20% of the initial value																				
D.F. (tan δ)	≤ 200% of the initial specified value																				
Leakage current	≤ The initial specified value																				
Shelf Life	<p>The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.</p> <table border="1"> <tr> <td>Capacitance change</td> <td>≤ ±20% of the initial value</td> </tr> <tr> <td>D.F. (tan δ)</td> <td>≤ 200% of the initial specified value</td> </tr> <tr> <td>Leakage current</td> <td>≤ The initial specified value</td> </tr> </table>	Capacitance change	≤ ±20% of the initial value	D.F. (tan δ)	≤ 200% of the initial specified value	Leakage current	≤ The initial specified value														
Capacitance change	≤ ±20% of the initial value																				
D.F. (tan δ)	≤ 200% of the initial specified value																				
Leakage current	≤ The initial specified value																				


DIMENSIONS [mm]

- Terminal Code : E



φD	5	6.3	8	10	12.5	16	18
φd	0.5	0.5	0.6	0.6	0.6	0.8	0.8
F	2.0	2.5	3.5	5.0	5.0	7.5	7.5
φD'	φD+0.5max.						
L'	L+1.5max.						

PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"

