

Product Summary

V _{BR Min}	IPP Max	С _{IN Тур}
6V	5A	1pF

Description And Applications

This new generation TVS is designed to protect sensitive electronics from the damage due to ESD. The combination of small size and high ESD surge capability makes it ideal for use in automotive applications.

- USB Modules
- HDMI Ports
- LVDS

Features & Benefits


- IEC 61000-4-2 (ESD): Air ±15kV, Contact ±8kV
- 1 Channel of ESD Protection
- Low Channel Input Capacitance of 1.0pF Typical
- Low Profile Package (0.53mm Max) and Ultra-Small PCB Footprint Area (1.08mm * 0.68mm Max) Suitable for Compact Portable Electronics
- Typically Used at High Speed Ports such as USB 2.0, IEEE1394, Serial ATA, DVI™, HDMI™, PCI
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data

- Case: X1-DFN1006-2
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208 @
- Weight: 0.001 grams (Approximate)



Bottom View



Ordering Information (Note 5)

Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
DRTR5V0U1LPQ-7B	Automotive	U6	7	8	10,000/Tape & Reel

Notes:	1. No purposely adde	d lead. Fully EU Directive 2	002/95/EC (RoHS), 201	1/65/EU (RoHS 2) & 2015/8	63/EU (RoHS 3) complian	t.
	2 See https://www.di	adaa aam/gualitu/laad fraa/	for more information ab	out Diados Incornerated's d	ofinitions of Hologon and	Antimony frog

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.

5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



U6 = Product Type Marking Code Bar Denotes Pin 1 or Cathode Side



Maximum Ratings ($@T_A = +25^{\circ}C$, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	Conditions
Peak Pulse Current	IPP	5	А	8/20µs, Per Figure 3
ESD Protection – Contact Discharge	V _{ESD_CONTACT}	±8	kV	Standard IEC 61000-4-2
ESD Protection – Air Discharge	Vesd_air	±15	kV	Standard IEC 61000-4-2

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Package Power Dissipation (Note 6)	PD	250	mW
Thermal Resistance, Junction to Ambient (Note 6)	R _{0JA}	500	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
Reverse Working Voltage	V _{RWM}	_	_	5.5	V	—
Reverse Current (Note 7)	IR	_	1	100	nA	V _R = 3.0V
Reverse Breakdown Voltage	V _{BR}	6.0	_	_	V	I _R = 1mA
Forward Voltage	VF	_	0.8	_	V	I _F = 1mA
Reverse Clamping Voltage, Positive Transients	V _{CL1}	_	10.0	_	V	$I_{PP} = 1A, t_p = 8/20 \mu s$
Reverse Clamping Voltage, Negative Transients	V _{CL2}	_	-1.7	_	V	I _{PP} = -1A, t _p = 8/20μs
Dynamic Resistance	R _{DYN}	_	0.9	_	Ω	I _R = 1A, t _p = 8/20μs
Capacitance	CIN		1.0	1.5	pF	$V_R = 0V$, f = 1MHz

Notes: 6. Device mounted on FR-4 PCB pad layout (2oz copper) as shown on Diodes Incorporated's suggested pad layout, which can be found on our website at http://www.diodes.com/package-outlines.html.


7. Short duration pulse test used to minimize self-heating effect.

8. For information on the impact of Diodes Incorporated's USB 2.0 compatible ESD protectors on signal integrity including eye diagram plots, please refer to AN77 at the following URL: https://www.diodes.com/design/support/application-notes/.









V_R, INSTANTANEOUS REVERSE VOLTAGE (V) Figure 5 Typical Reverse Characteristics

DRTR5V0U1LPQ





Figure 6 Typical Total Capacitance vs. Reverse Voltage



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

X1-DFN1006-2




X1-DFN1006-2						
Dim	Min	Max	Тур			
Α	0.47	0.53	0.50			
A1	0	0.05	0.03			
b	0.45	0.55	0.50			
D	0.95	1.075	1.00			
ш	0.55	0.675	0.60			
e	-	-	0.40			
L	0.20	0.30	0.25			
R	0.05	0.15	0.10			
All	All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

X1-DFN1006-2



Dimensions	Value (in mm)
С	0.70
G	0.30
Х	0.40
X1	1.10
Y	0.70



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com