
KEMET Part Number: M39003/09-2017

(T262C127K010BS, M39003/09-2017{KEM}, CSR21C127KB)



T262 CSR21, Tantalum, MnO2 Tantalum, Military/High Reliability, 120 uF, 10%, 10 VDC, 70 mOhms



Dimensions		
D	7.34mm +/-0.25mm	
L	17.42mm +/-0.79mm	
L2	20.88mm	
LL	38.1mm +/-6.35mm	
F	0.64mm +/-0.05mm	
G	3.46mm +0.79mm	

Packaging Specifications		
Packaging:	Tray	
Packaging Quantity:	20	

General Ir	General Information		
Series:	T262 CSR21		
Dielectric:	MnO2 Tantalum		
Style:	Axial Hermetic		
Description:	Axial, Solid Tantalum, Hermetically Sealed, Military, CSR21 Style		
Features:	Low ESR, High Current		
RoHS:	No		
Prop 65:	WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov.		
REACH:	SVHC (Pb – CAS 7439-92-1)		
SCIP Number:	bee1eed4-5fec-4214-9f43-620c5b2	22	
Termination:	Lead (SnPb)		
Lead:	Wire Leads		
Qualifications:	MIL-PRF-39003, CSR21		
AEC-Q200:	No		
Construction:	Hermetic		
Miscellaneous:	Ripple Current Rating Shown Is At 40Khz And 25C; ESR Is Per MIL-PRF-39003/9.		
Notes:	Dimensions Include Insulating Sleeve. Lead Length Shown Is For Parts Supplied With Bulk Packaging, When Supplied On T&R Or Ammo, Lead Length Is Determined By Taping Specification.		

Specifications		
Capacitance:	120 uF	
Capacitance Tolerance:	10%	
Voltage DC:	10 VDC (85C), 9 VDC (125C Surge), 0.1 VDC (125C Reverse)	
Temperature Range:	-55/+125°C	
Dissipation Factor:	8% 1kHz 25C	
Failure Rate:	B (0.1%/1000 Hrs)	
Resistance:	0.07 Ohms (100kHz)	
Ripple Current:	3200 mAmps (100kHz)	
Leakage Current:	6 uA	
Testing and Reliability:	Standard Testing To MIL- PRF-39003	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

