6-Line ESD Protection Diode Array in LLP75

FEATURES

- Ultra compact LLP75-7L package
- 6-line ESD protection
- Low leakage current I_B < 1 μA
- Low load capacitance C_D = 40 pF
- ESD immunity acc. IEC 61000-4-2 ± 30 kV contact discharge ± 30 kV air discharge
- Working voltage range V_{RWM} = 5 V
- e4 precious metal (e.g. Ag, Au, NiPd, NiPdAu) (no Sn)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

ORDERING INFORMATION						
DEVICE NAME ORDERING CODE		TAPED UNITS PER REEL (8 mm TAPE ON 7" REEL)	MINIMUM ORDER QUANTITY			
VESD05A6-HAF	VESD05A6-HAF-GS08	3000	15 000			

PACKAGE DATA						
DEVICE NAME PACKAGE TYPE WEIGHT		MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS		
VESD05A6-HAF	LLP75-7L	AS	4.2 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	Peak temperature max. 260 °C

ABSOLUTE MAXIMUM RATINGS							
RATING	TEST CONDITION	SYMBOL	VALUE	UNIT			
Peak pulse current	BiAs-mode: each input (pin 1 to pin 6) to ground acc. IEC 61000-4-5; t _p = 8/20 μs; single sh	I _{PPM}	5	А			
Peak pulse power	BiAs-mode: each input (pin 1 to pin 6) to ground acc. IEC 61000-4-5; t _p = 8/20 μs; single sh	P _{PP}	60	W			
ESD immunity	Acc. IEC61000-4-2; 10 pulses BiAs-Mode: each input (pin 1 to pin 6) to ground (pin 2)	Contact discharge	V _{ESD}	± 30	kV		
		Air discharge	V _{ESD}	± 30	kV		
Operating temperature	Junction temperature	TJ	-40 to +125	°C			
Storage temperature			T _{STG}	-55 to +150	°C		

click logo to get started

MARKING (example only)

YY = type code (see table below)

DESIGN SUPPORT TOOLS

Dot = pin 1 marking XX = date code

Models Available

19371



www.vishay.com

ORDERING INFORMATION					
DEVICE NAME ORDERING CODE		MINIMUM ORDER QUANTITY			
VESD05A6-HAF-GS08	3000	15 000			
	ORDERING CODE	ORDERING CODE TAPED UNITS PER REEL (8 mm TAPE ON 7" REEL)			

Rev. 1.7,	07-Jan-2019
-----------	-------------




(5-2008)




APPLICATION NOTE:

a) With the VESD05A6-HAF 6 different signal or data lines can be clamped to ground. Due to the different clamping levels in forward and reverse direction the VESD05A6-HAF clamping behavior is bidirectional and asymmetrical (BiAs).



b) If symmetrical clamping behaviour is required the VESD05A6-HAF can also be used as a bidirectional symmetrical protection device protecting up to 5 lines. In this case pin 7 must not be connected.




ELECTRICAL CHARACTERISTICS (Between pin 1, 2, 3, 4, 5 or 6, and pin 7) (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITIONS/REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Protection paths	Number of lines which can be protected	N _{channel}	-	-	6	lines	
Reverse stand-off voltage	Max. reverse working voltage	V _{RWM}	-	-	5	V	
Reverse voltage	at I _R = 1 μA	V _R	5	-	-	V	
Max. reverse current	at V _R = 5 V	I _R	-	< 0.1	1	μA	
Reverse breakdown voltage	at I _R = 1 mA	V _{BR}	6	6.6	7.5	V	
	at I _{PP} = 1 A	V _C	-	8.1	10	V	
Reverse clamping voltage	at I _{PP} = I _{PPM} = 5 A	V _C	-	11.3	12	V	
Forward clamping voltage	at I _{PP} = 1 A	V _F	-	1.5	1.8	V	
	at I _{PP} = I _{PPM} = 5 A	V _F	-	3.2	4.5	V	
Line capacitance	at V _R = 0 V; f = 1 MHz	CD	-	40	50	pF	
	at V _R = 2.5 V; f = 1 MHz	CD	-	24	-	pF	


Note

• BiAs mode (between pin 1, 2, 3, 4, 5 or 6 and pin 7)



TYPICAL CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified)








Fig. 2 - 8/20 µs Peak Pulse Current Wave Form acc. IEC 61000-4-5




Fig. 3 - Typical Capacitance $C_{D}\, vs.$ Reverse Voltage V_{R}




Fig. 4 - Typical Forward Current I_{F} vs. Forward Voltage V_{F}




Fig. 5 - Typical Reverse Voltage V_R vs. Reverse Current I_R




Fig. 6 - Typical Peak Clamping Voltage V_C vs. Peak Pulse Current I_{PP}


Rev. 1.7, 07-Jan-2019

3

Document Number: 81311

For technical questions, contact: <u>ESDprotection@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>





www.vishay.com

SHAY

Fig. 7 - Typical Clamping Performance at + 8 kV Contact Discharge (acc. IEC 61000-4-2)




Fig. 8 - Typical Clamping Performance at - 8 kV Contact Discharge (acc. IEC 61000-4-2)





Fig. 9 - Typical Peak Clamping Voltage at ± ESD Contact Discharge (acc. IEC 61000-4-2)

4

For technical questions, contact: <u>ESDprotection@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>




PACKAGE DIMENSIONS in millimeters (Inches): LLP75-7L



5









Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.